

Harness Component Table AC Servo Motor Compatible Harnesses

Series Name	Harness Type	Model	Connector 1 Part Number	Related Components	Connector 2 Part Number	Related Components	Crimp Terminal Used	A (C) Cable Part Number	B (D) Cable Part Number
MR-J2W	Power Supply OP.2048	SVPM-J3W1	F35FDC-04V-K	LF3F-41GF-P2.0	JM4F04SJ1-R	ST-TMH-S-C18-100(A534G)	-	(A) NAECT-18-4 (O4711) (C) NAGUCSB-16-4 (O4219)	(B) NAECTR-18-4 (O4226) (D) NAGUCRSB-16-4 (O4533)
		SVPM-J3W1B	-	-	JM4F02S1-R	ST-TMH-S-C18-100(A534G)	-	(A) NAWC-21-1P (O4711) (C) NAWCSB-21-1P (O4325)	(B) NAMF-21-1P (O4537) (D) NAMFSB-21-1P (O4539)
	Encoder OP.2048	SVEM-J3W1	38210-0100FD	38310-3200-008	1674320-1	-	-	NAUCSB-23-3P (O4327)	NAMFSB-23-3P (O4539)
MR-J3-□	Power Supply OP.2051	SVPM-J3HF1	-	-	JM4F04S1-R	ST-TMH-S-C18-100(A534G)	-	(A) NAECT-18-4 (O4711) (C) NAGUCSB-16-4 (O4219)	(B) NAECTR-18-4 (O4226) (D) NAGUCRSB-16-4 (O4445)
		SVPM-J3HF2	-	-	CE05-6A18-10SD-0-BSS (O3320)	CE3057-10A-1-D	-	(A) NAECT-16-4 (O4711) (C) NAGUCSB-16-4 (O4205)	(B) NAECTR-16-4 (O4712) (D) NAGUCRSB-16-4 (O4420)
		SVPM-J3HF3	-	-	CE05-6A18-10SD-0-BSS (O3320)	CE3057-10A-1-D	-	(A) NAECT-14-4 (O4711) (C) NAGUCSB-14-4 (O4205)	(B) NAECTR-14-4 (O4712) (D) NAGUCRSB-14-4 (O4420)
		SVPM-J3HF5	-	-	CE05-6A22-22SD-0-BSS (O3320)	CE3057-12A-1-D	-	(A) NAECT-14-4 (O4711) (C) NAGUCSB-14-4 (O4205)	(B) NAECTR-14-4 (O4712) (D) NAGUCRSB-14-4 (O4420)
		SVPM-J3HF6	-	-	CE05-6A22-22SD-0-BSS (O3320)	CE3057-12A-1-D	-	NAECT-10-4 (O4711)	NAECTR-10-4 (O4712)
		SVPM-J3HF7	-	-	CE05-6A24-10SD-0-BSS (O3320)	CE3057-16A-1	RVW5-5-4YE	(A) NAECT-10-4 (O4711) (C) NAGUCSB-10-4 (O4205)	(B) NAECTR-10-4 (O4712) (D) NAGUCRSB-10-4 (O4420)
		SVPM-J3HF8	-	-	CE05-6A32-17SD-0-BSS (O3320)	-	-	NAECT-6-4 (O4711)	NAECTR-6-4 (O4712)
		SVPM-J3HF9	-	-	CE05-6A22-23SD-0-BSS (O3320)	-	-	NAECT-14-4 (O4711)	NAECTR-14-4 (O4712)
		SVPM-J3HF10	-	-	CE05-6A24-10SD-0-BSS (O3320)	-	-	NAECT-10-4 (O4711)	NAECTR-10-4 (O4712)
		SVPM-J3HF1B	-	-	-	JM4F02S1-R	ST-TMH-S-C18-100(A534G)	-	(A) NAWC-21-1P (O3230) (C) NAWCSB-21-1P (O4327)
	Encoder OP.2053	SVPM-J3HF2B	-	-	CM10-SP2S-L(D6) (O3364)	CM10-422S(C)DB-100	-	(A) NAWC-16-2 (O4203) (C) NAGUCSB-16-2 (O4205)	(B) NAWCR-16-2 (O4417) (D) NAGUCRSB-16-2 (O4439)
		SVPM-J3HF7B	-	-	DMS3106A-10SL-4-S-BSS (O3219)	YS010-5-8	RVW2-4BU	NABUC-16-2 (O4203)	NABUCR-16-2 (O4417)
		SVEM-J3HF1	38210-0100FD (Not Available)	38310-3200-008	1674320-1 (Not Available)	-	-	NAUCSB-23-3P (O4327)	NAMFSB-23-3P (O4539)
		SVEM-J3HF2	38210-0100FD (Not Available)	38310-3200-008	CM10-SP10S-M(D6) (O3364)	CM10-422S(C)DB-100	-	NAUCSB-23-3P (O4327)	NAMFSB-23-3P (O4539)
		SVEM-J3HF1M	1-172169-9	316454-1 / 1473226-1	1674320-1	-	-	NAUCSB-23-4P	NAMFSB-25-4P
		SVEM-J3HF1L-C20	38210-0100FD (Not Available)	38310-3200-008	1-172161-9	170359-1	-	NAUCSB-23-5P (O4327)	-
		SVEM-J3HF1L-C30	38210-0100FD (Not Available)	38310-3200-008	1-172161-9	170359-1	-	NAUCSB-23-6P (O4327)	-
		SVEM-J3HF1L-D20	38210-0100FD	38310-3200-008	1-172161-9	170359-1	-	-	NAMFSB-25-6P (O4539)
		SVEM-J3HF1L-D50	38210-0100FD	38310-3200-008	1-172161-9	170359-1	-	-	NAMFSB-25-6P (O4539)
		SVEM-J3HF2L	38210-0100FD (Not Available)	38310-3200-008	CM10-SP10S-M (O3364)	CM10-422S(C)DB-100	-	NAUCSB-23-6P (O4327)	NAMFSB-25-6P (O4539)
	Signal Control OP.2055	SVSM-J3QD1	FCN-361J040-AU (O3055)	FCN-360C040-B	10150-3000PE (O3074)	10350-52F0-008	RVW1-25-3.5RE	NA30276-5P NA30276-6P (O4347)	-
		SVSM-J3QD2	FCN-361J040-AU (O3055)	FCN-360C040-B	10150-3000PE (O3074)	10350-52F0-008	RVW1-25-3.5RE	NA30276-5P NA30276-6P (O4347)	-
		SVSM-J3AD	10136-3000PE (O3074)	10336-52F0-008	10150-3000PE (O3074)	10350-52F0-008	RVW1-25-3.5RE	NA30276-6P (O4347)	-
		SVPM-J2HC1	-	-	5559-04P-210 (O3486)	5559PBT3L	RVW1-25-4RE	(A) NAECT-16-4 (O4711) (C) NAGUCSB-16-4 (O4205)	(B) NAECTR-16-4 (O4712) (D) NAGUCRSB-16-4 (O4419)
		SVPM-J2HC2	-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW2-4BU	NAECT-16-4 (O4347)	NAECTR-16-4 (O4712)
		SVPM-J2HC3	-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW2-4BU	(A) NAECT-14-4 (O4711) (C) NAGUCSB-14-4 (O4205)	(B) NAECTR-14-4 (O4712) (D) NAGUCRSB-14-4 (O4419)
	Power Supply OP.2057	SVPM-J2HC4	-	-	CE05-6A24-10SD-0-BSS (O3320)	CE3057-16A-1	RVW5-5-4YE	NAECT-12-4 (O4712)	NAECTR-12-4 (O4712)
		SVPM-J2HC5	-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW5-5-4YE	(A) NAECT-12-4 (O4712) (C) NAGUCSB-12-4 (O4205)	(B) NAECTR-12-4 (O4712) (D) NAGUCRSB-12-4 (O4419)
		SVPM-J2HC6	-	-	CE05-6A24-10SD-0-BSS (O3320)	CE3057-16A-1	RVW5-5-4YE	(A) NAECT-10-4 (O4712) (C) NAGUCSB-10-4 (O4205)	(B) NAECTR-10-4 (O4712) (D) NAGUCRSB-10-4 (O4419)
		SVPM-J2HC7	-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW5-5-4YE	NAECT-10-4 (O4712)	NAECTR-10-4 (O4712)
SVPM-J2HC1B		-	-	5559-06P-210 (O3486)	5559PBT3L	RVW1-25-4RE	(A) NAECT-16-6 (O4712) (C) NAGUCSB-16-6 (O4205)	(B) NAECTR-16-6 (O4712) (D) NAGUCRSB-16-6 (O4419)	
SVPM-J2HC2B		-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW2-4BU	(A) NAECT-16-6 (O4712) (C) NAGUCSB-16-6 (O4205)	(B) NAECTR-16-6 (O4712) (D) NAGUCRSB-16-6 (O4419)	
SVPM-J2HC3B		-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW2-4BU	(A) NAECT-14-6 (O4712) (C) NAGUCSB-14-6 (O4205)	(B) NAECTR-14-6 (O4712) (D) NAGUCRSB-14-6 (O4419)	
SVPM-J2HC4B		-	-	DMS3106A-10SL-4-SID190 (O3219)	YS010-5-8	RVW2-4BU	NABUC-16-2 (O4203)	NABUCR-16-2 (O4417)	
SVPM-J2HC5B		-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW5-5-4YE	NAECT-12-6 (O4711)	NAECTR-12-6 (O4417)	
SVPM-J2HC6B		-	-	DMS3106A-10SL-4-S-BSS (O3219)	YS010-5-8	RVW2-4BU	NABUC-16-2 (O4203)	NABUCR-16-2 (O4417)	
SVPM-J2HC7B		-	-	CE05-6A22-23SD-0-BSS (O3320)	CE3057-12A-1	RVW1-25-4RE	(A) NAECT-12-6 (O4711) (C) NAGUCSB-12-6 (O4205)	(B) NAECTR-12-6 (O4712) (D) NAGUCRSB-12-6 (O4419)	
SVPM-J2HC8B		-	-	CE05-6A24-10SD-0-BSS (O3320)	CE3057-16A-1	RVW1-25-4RE	NAECT-16-6 (O4711)	NAECTR-16-6 (O4712)	
Encoder OP.2059		SVEM-J2HC1	10120-3000PE (O3074)	10320-52F0-008	1-172161 (O3433)	170359-1.MT1-0002	-	NAUCSB-27-5P (O4327)	NAMFSB-25-5P (O4321)
		SVEM-J2HC2	10120-3000PE (O3074)	10320-52F0-008	DMS3106A-20-29-S-BSS (O3219)	CE3057-12A-3	-	NAUCSB-27-4P (O4327)	NAMFSB-25-4P (O4321)
	SVEM-J2HC1L	10120-3000PE (O3074)	10320-52F0-008	1-172161 (O3433)	170359-1.MT1-0002	-	NAUCSB-23-7P (O4327)	NAMFSB-25-7P (O4321)	
	SVEM-J2HC2L	10120-3000PE (O3074)	10320-52F0-008	DMS3106A-20-29-S-BSS (O3219)	CE3057-12A-3	-	NAUCSB-23-5P (O4327)	NAMFSB-25-5P (O4321)	

Device Compatible Harnesses

- Harness Selection Method
- PLC Compatible Harnesses
- Relay Terminal Compatible Harnesses
- Touch Panel Compatible Harnesses
- AC Servo Motor Compatible Harnesses
- Single-Axis Robot Compatible Harnesses
- Stepper Motor Compatible Harnesses
- RS-232C Harnesses
- I/O Board Compatible Harnesses
- Image Sensor Compatible Harnesses
- Sensor Compatible Harnesses