

Knurled Knobs with Pad / Knurled Knobs / Knurled Knobs

Counterbored Slotted

Knurled Knobs with Pad RoHS 10

Type	Material	Surface Treatment	Material
NOOSP	303 Stainless Steel	Brushed Finish	Polyacetal (White)
NOOSC	303 Stainless Steel	Brushed Finish	Free-Cutting Brass (C36000 Brass)

Part Number	Type	M (Coarse)	L		A	D	d1	l	l1	Unit Price	
			NOOSP	NOOSC							
Polyacetal NOOSP	4	3	6	10	2.5	12	1.5	1	0.5		
		4	6	10	16	3.5	16	2	1.2	1	
	5	5	10	16	20	4	20	3	1.4	1	
		6	10	16	20	5	24	4	1.5	1	
	8	8	16	20	25	6	30	6	2	2	
		10	20	25	30	8	36	8	2.5	2	

Ordering Example: Part Number - L Days to Ship [Configure Online](#) Price [Configure Online](#)

Example: NOOSP6 - 10

Counterbored Knurled Knobs RoHS 10

Type	Accessories	Material	Material
NKOSJ	Screw, Nut	303 Stainless Steel	303 Stainless Steel
NKOSJN	Without Screw and Nut	Steel	-

Length of the thread part is changeable by exchanging with a commercially-available bolt.

Part Number	Type	M	Selectable only for NKOSJ	(L1)	D	D1	B	d1	(d2)	A	S	t	Unit Price	
													NKOSJ	NKOSJN
With Screw and Nut NKOSJ	4	12	6.6	16	7.5	11	9	8.1	8	2.4	5			
		15	9.6	16	7.5	11	9	8.1	8	2.4	5			
		20	14.6	16	7.5	11	9	8.1	8	2.4	5			
		25	19.6	16	7.5	11	9	8.1	8	2.4	5			
		30	24.6	16	7.5	11	9	8.1	8	2.4	5			
		35	29.6	16	7.5	11	9	8.1	8	2.4	5			
Without Screw and Nut NKOSJN	5	15	8.8	20	9	12	10	9.2	9	3.2	6			
		20	13.8	20	9	12	10	9.2	9	3.2	6			
		25	18.8	20	9	12	10	9.2	9	3.2	6			
		30	23.8	20	9	12	10	9.2	9	3.2	6			
		35	28.8	20	9	12	10	9.2	9	3.2	6			
		40	33.8	20	9	12	10	9.2	9	3.2	6			
	6	15	8.4	24	11	14	12	11.5	10	3.6	7			
		20	13.4	24	11	14	12	11.5	10	3.6	7			
		25	18.4	24	11	14	12	11.5	10	3.6	7			
		30	23.4	24	11	14	12	11.5	10	3.6	7			
		35	28.4	24	11	14	12	11.5	10	3.6	7			
		40	33.4	24	11	14	12	11.5	10	3.6	7			

Knurled Knobs - Slotted RoHS 10

Type	Material	Surface Treatment
NOBW	1215 Carbon Steel	Trivalent Chromate
NOOSW	303 Stainless Steel	Brushed Finish

Part Number	Type	M (Coarse)	L		D	A	l	t	W	Unit Price	
			NOBW	NOOSW							
NOBW	4	3	6	10	5	2.5	1	1.5	1.8		
		4	6	10	16	7	3.5	1.2	1.5	1.8	
	5	5	10	16	20	11	4	1.4	2	1.8	
		6	10	16	20	13	5	1.5	2	1.8	

Ordering Example: Part Number - L Days to Ship [Configure Online](#) Price [Configure Online](#)

Example: NKOSJ4 - 12, NOBW3 - 10

Knurled Knob Screws / Knurled Knob Screws - SR Tip

Knurled Knob Screws RoHS 10

Type	Material	Surface Treatment	Accessories
Short	C36000 Brass	BD Brass (JIS)	Chromate
NRS	NRL	303 Stainless Steel	-
NRSS	NRLS	303 Stainless Steel	-

Short

Part Number	Type	M (Coarse)	L	L1	D	D1	H	Mass (g)	Unit Price	
									NRS	NRSS
NRS (Brass)	4	10	20	10	12					
		15	25	15	13					
		20	30	20	14					
NRSS (Stainless Steel)	5	10	20	12	15					
		15	25	12	15					
		20	30	12	15					
	6	10	22	18	24					
		15	27	18	25					

Long

Part Number	Type	M (Coarse)	L	L1	L2	D	D1	D2	H	Mass (g)	Unit Price	
											NRL	NRLS
NRL (Brass)	4	20	30	12	10	3	14					
		25	35	15	10	3	14					
		30	40	15	10	3	14					
	5	20	30	12	15	8	15					
		25	35	12	15	8	16					
		30	40	12	15	8	16					
NRLS (Stainless Steel)	6	30	42	15	18	4.5	27					
		35	47	15	18	4.5	27					
		40	52	15	18	4.5	28					
	8	40	52	24	14	6	29					
		50	62	24	14	6	50					
		50	62	24	14	6	53					

Ordering Example: Part Number - L Days to Ship [Configure Online](#)

Example: NRS5 - 15, NRL8 - 50

Price [Configure Online](#)

Alterations: Part Number - LC - (FC) Days to Ship [Configure Online](#)

Example: NRLS8 - LC30 - FC20

Alteration	Code	Spec.	Price Adder
	LC	L dimension can be specified in 1mm increment. Ordering Code LC30	
		M LC	
		4 10-30	
		5 10-40	
		6 10-50	
		8 20-50	
		NRSS is applicable to M4-6.	

Alteration	Code	Spec.	Price Adder
	FC	Threads can be specified in 1mm increment. Ordering Code FC20 M<FC:LC-2	Free of Charge
		FC is only available in combination with LC.	
		Applicable to NRLS only.	

Knurled Knob Screws - SR Tip RoHS 10

Type	Material
Short	303 Stainless Steel
NRSSR	NRLSR

Short

Part Number	Type	M (Coarse)	L	L1	D	D1	H	SR	Mass (g)	Unit Price
NRSSR	4	10	20	10	4	12				
		15	25	15	4	13				
		20	30	20	5	14				
	5	10	20	12	5	15				
		15	25	12	5	15				
		20	30	12	6	24				
	6	10	22	18	6	24				
		15	27	18	6	25				

Long

Part Number	Type	M (Coarse)	L	L1	L2	D	D1	D2	H	SR	Mass (g)	Unit Price
NRLSR	4	20	30	12	10	3	4	14				
		25	35	15	10	3	4	14				
		30	40	15	10	3	4	14				
	5	20	30	12	15	8	5	15				
		25	35	12	15	8	5	16				
		30	40	12	15	8	5	16				
	6	30	42	15	18	4.5	6	27				
		35	47	15	18	4.5	6	27				
		40	52	15	18	4.5	6	28				
	8	40	52	24	14	6	6	29				
		50	62	24	14	6	8	50				
		50	62	24	14	6	8	53				

Ordering Example: Part Number - L Days to Ship [Configure Online](#)

Example: NRSSR4 - 10, NRLSR6 - 35

Price [Configure Online](#)