

LIFTER CUSHION PINS / BUSHINGS FOR LIFTER CUSHION PINS

PLATE LIFTER PINS / LIFTER PLATE STOPPERS

Lifter cushion pins RoHS

DTCA

This product was discontinued in 2017.

Catalog No. : DTCA

DTCB

section : Induction hardened
 S45C
 55HRC~

d	d1	d2	Catalog No.		L 5mm increments	S 5mm increments	Base unit price 1~9 pieces	
			Type	D			DTCA	DTCB
38	29	26	DTCA	30	100~160	50~110		
					165~240	50~190		
					245~275	50~225		
48	39	36	DTCB	40	100~160	50~110	Quotation	
					165~280	50~230		
					285~360	50~310		
58	49	46	DTCB	50	160~220	50~170		
					225~300	50~250		
					305~410	50~360		
					415~460	50~410		

Order Catalog No. - L - S
DTCB 50 - 300 - 100

Days to Ship Quotation

Price Quotation

Bushings for lifter cushion pins RoHS

TGF (Cast type)
TGW (Copper alloy type)

TGW S45C Copper alloy
 Special solid lubricant (embedded)

TGF was discontinued in 2017.

D1	h	L	Catalog No.		Base unit price 1~9 pieces	
			Type	D	TGF	TGW
50	±0.008	10	TGF (Cast type)	30		Quotation
60	±0.0095	15	TGW (Copper alloy type)	40		
70					50	

Order Catalog No. : TGW 30

Price Quotation

Days to Ship Quotation

Plate lifter pins RoHS **LCP**

S45C
 50HRC~
 (Induction hardened)

d	T	H	Catalog No.		L 10mm increments	S 1mm increments	Base unit price 1~9 pieces
			Type	D			
10	18	18	LCP	13	100~200	10~20	Quotation
					210~250		
13	21	21	LCP	16	100~200	15~30	Quotation
					210~300		
16	25	25	LCP	20	100~190	15~40	Quotation
					200~300		
					310~400		
20	30	30	LCP	25	100~240	15~50	Quotation
					250~300		
					310~400		
25	40	40	LCP	32	100~240	15~50	Quotation
					250~300		
					310~400		
					410~500		

Price Quotation

Order Catalog No. - L - S
LCP 20 - 250 - 25

Days to Ship Quotation

Alterations Catalog No. - L(LC) - S - (MC)
LCP 20 - LC248 - 25 - MC

Alteration	Code	Spec.	1Code																	
	LC	Full length change Lmin ≤ LC < Lmax. 1mm increments	Quotation																	
	MC	Tapping <table border="1"> <tr> <td>D</td> <td>13</td> <td>16</td> <td>20</td> <td>25</td> <td>32</td> </tr> <tr> <td>M</td> <td>8</td> <td>8</td> <td>10</td> <td>12</td> <td>16</td> </tr> <tr> <td>ℓ</td> <td colspan="5">2XM</td> </tr> </table>		D	13	16	20	25	32	M	8	8	10	12	16	ℓ	2XM			
D	13	16	20	25	32															
M	8	8	10	12	16															
ℓ	2XM																			

Lifter plate stoppers RoHS

BSE (Fixed L dimension type)
BST (Configurable L dimension type)

S45C

B	T	C	X	Y	P	d1	d2	h	Catalog No.		Base unit price 1~9 pieces
									Type	A	
38	10	30	15	15	30	11	18	12	BSE	60	40 50 60
											70 80
											50 60
45	13	36	20	18	40	14	20	14	BSE	80	70 80 90
											100
60	15	50	25	25	50	18	26	18	BSE	100	60
											70 80 90
											100

B	T	C	X	Y	P	d1	d2	h	Catalog No.		Base unit price 1~9 pieces
									Type	A	
38	10	30	15	15	30	11	18	12	BST	60	41~ 59
											61~ 79
											51~ 59
45	13	36	20	18	40	14	20	14	BST	80	61~ 89
											91~ 99
											61~ 89
60	15	50	25	25	50	18	26	18	BST	100	91~ 99
											101~ 120

⚠ If L is 100 or less and an even 10mm increment, please use BSE instead of BST.

Order Catalog No. - L
BSE 80 - 70
BST 60 - 43

Days to Ship Quotation

Price Quotation