




OIL-FREE PAD GUIDE BLOCKS



CAM UPPER PLATES



CMG11

2-C Bore holes For M16 Soc.Hd.Scr.
2-φ 16 G6

Special solid lubricant (embedded) & induction hardened


□ S45C
Special solid lubricant (embedded)
■ 40HRC~ (Induction hardened)

T	L	ℓ ₁	ℓ ₂	ℓ ₃	ℓ ₄	NAAMS Code	Catalog No.	
							Type	Code
75	80	25	35	40	55	G118007	CMG11	8007
100						G118010		8010
125						G118012		8012
75	95	40	50	55	70	G119507		9507
100						G119510		9510
125						G119512		9512
75	120	65	75	80	95	G111207	1207	
100						G111210	1210	
125						G111212	1212	

Order
CMG11 8007

Days to Ship

Price



CMR21
CMR22 (Without bolt holes type)

Special solid lubricant (embedded) & induction hardened

□ S45C
Special solid lubricant (embedded)
■ 40HRC~ (Induction hardened)

W	L	N (Holes)	w ₁	w ₂	ℓ ₁	ℓ ₂	ℓ ₃	ℓ ₄	NAAMS Code		Catalog No.	
									With bolt holes	Without bolt holes	Type	code
100	200	3	55	80	100	—	—	175	R211020	R221020	CMR21 CMR22	1020
	250	4			90	—	160	225	R211025	R221025		1025
	315	5			90	158	225	290	R211031	R221031		1031
	350				100	175	250	325	R211035	R221035		1035
	400				115	200	285	375	R211040	R221040		1040
	450				125	225	325	425	R211045	R221045		1045
125	200	3	65	105	100	—	—	175	R211220	R221220	CMR21 CMR22	1220
	250	4			90	—	160	225	R211225	R221225		1225
	315	5			90	158	225	290	R211231	R221231		1231
	350				100	175	250	325	R211235	R221235		1235
	400				115	200	285	375	R211240	R221240		1240
	450				125	225	325	425	R211245	R221245		1245
150	200	3	65	130	100	—	—	175	R211520	R221520	CMR21 CMR22	1520
	250	4			90	—	160	225	R211525	R221525		1525
	315	5			90	158	225	290	R211531	R221531		1531
	350				100	175	250	325	R211535	R221535		1535
	400				115	200	285	375	R211540	R221540		1540
	450				125	225	325	425	R211545	R221545		1545

Order
CMR21 1025

Days to Ship

Price

NAAMS