

Brackets for Device Stands

These Brackets can be combined with struts on next page to construct custom configurations. Other useful accessories are also contained in this section to assist your custom device stand designs.


Round Brackets

Material	Surface Treatment	Included Hardware	Type
Alloy Cast Iron Class No. 35	Black Oxide	Set Screws (2 pcs)	U-CSTF

Detail Dimensions P.441

Surface Roughness:  
Unless otherwise specified

Part No.					\$ Unit Price
Type	D				
	Callout	Nominal	Tolerance		Qty. 1~4
U-CSTF	0.38	3/8	0.3756	0.3750	11.60
	0.50	1/2	0.5007	0.5000	11.80
	0.63	5/8	0.6257	0.6250	12.10
	0.75	3/4	0.7508	0.7500	12.70
	1.00	1"	1.0008	1.0000	17.60

Order Example

Part No.

TypeD

U-CSTF0.63

The part number consists only of the fields with blue characters.

For detailed bracket dimensions, please refer to P.441.


Square Brackets

Material	Surface Treatment	Included Hardware	Type
Alloy Cast Iron Class No. 35	Black Oxide	Set Screws (2 pcs)	U-ASTF

Detail Dimensions P.443

Surface Roughness:  
Unless otherwise specified


Part No.					\$ Unit Price
Type	D				Qty. 1~4
	Callout	Nominal	Tolerance		
U-ASTF	0.38	3/8	0.3756	0.3750	11.30
	0.50	1/2	0.5007	0.5000	11.60
	0.63	5/8	0.6257	0.6250	11.90
	0.75	3/4	0.7508	0.7500	12.50
	1.00	1"	1.0008	1.0000	16.50


Order Example

Part No.

TypeD

U-ASTF0.75

The part number consists only of the fields with blue characters.

For detailed bracket dimensions, please refer to P.443.

Days to Ship

1 Day

Price

Quantity Discount Rate				
Quantity	1~4	5~9	10~19	20~
Rate	—	2%	3%	5%

For larger quantity orders "Days to Ship" may differ from published catalog term. P.29


Side Mounting Brackets

Material	Surface Treatment	Included Hardware	Type
Alloy Cast Iron Class No. 35	Black Oxide	Set Screws (2 pcs)	U-SSTF

Detail Dimensions P.445

Surface Roughness:  
Unless otherwise specified


Part No.					B	d1	\$ Unit Price
Type	D						Qty. 1~4
	Callout	Nominal	Tolerance				
U-SSTF	0.38	3/8	0.3756	0.3750	1.378	0.236	17.80
	0.50	1/2	0.5007	0.5000	1.378	0.236	18.30
	0.63	5/8	0.6257	0.6250	1.575	0.394	18.90
	0.75	3/4	0.7508	0.7500	1.772	0.461	20.20
	1.00	1"	1.0008	1.0000	2.362	0.598	23.70


Order Example

Part No.

TypeD

U-SSTF0.50

The part number consists only of the fields with blue characters.

For detailed bracket dimensions, please refer to P.445.


Compact Brackets

Material	Surface Treatment	Included Hardware	Type
1045 Steel	Electroless Nickel Plating	Set Screws (2 pcs)	U-MFSTF

Detail Dimensions P.447

Surface Roughness:  
Unless otherwise specified


Part No.					\$ Unit Price
Type	D				
	Callout	Nominal	Tolerance		Qty. 1~4
U-MFSTF	0.38	3/8	0.3756	0.3750	11.90
	0.50	1/2	0.5007	0.5000	12.60
	0.63	5/8	0.6257	0.6250	14.40
	0.75	3/4	0.7508	0.7500	17.00
	1.00	1"	1.0008	1.0000	20.60


Order Example

Part No.

TypeD

U-MFSTF 1.00

The part number consists only of the fields with blue characters.

For detailed bracket dimensions, please refer to P.447.

Days to Ship

1 Day

Price

Quantity Discount Rate				
Quantity	1~4	5~9	10~19	20~
Rate	—	2%	3%	5%

For larger quantity orders "Days to Ship" may differ from published catalog term. P.29