

Pull Handles for Aluminum Extrusions

Arched Pull Handles **RoHS10**

UWSD

Feature: Products intended for aesthetics as well as easier grip design.

Material: 304 Stainless Steel
Surface Treatment: Buffed Finish

Part Number	L1	H	h	H1	Allowable Load (N)	Mass (g)	Unit Price
Type	L						
UWSD	100	139	42	27	22	500	337
	150	190	44	29	20		434

EX Example



Cast Pull Handles **RoHS10**

UWASND

Material: 304 Stainless Steel
Surface Treatment: Buffed Finish

Part Number	L1	H	h	T	A	W	R	N	Allowable Load (N)	Mass (g)	Unit Price
Type	L							Through	Countersunk		
UWASND	80	96	32	20	6	18	12	20		97	
	100	116						4.5	8.5	116	
	150	170	46	30	9	22	16	6.5	12.5	301	
	200	220	46	30	9	22	16	6.5	12.5	354	

Ordering Example

Part Number: UWSD100
UWASND80

Days to Ship **Configure Online**

Price **Configure Online**

Aluminum Pull Handles **RoHS10**

Type	Material	Surface Treatment
HHDF	Aluminum Alloy	Electrostatic Paint (Mat Black)
HHDFL	Aluminum Alloy	Barrel Grinding
HHDFA	Aluminum Alloy	Buffed Finish

Material: Aluminum Alloy
Surface Treatment: Buffed Finish

Part Number		Applicable Extrusion (Series)	L	L ₁	H	h	R	C	L _r	Mass (g)	Screw / Nut				Unit Price		
Type	A										Screw	Quantity	Nut	Quantity	HHDF	HHDFL	HHDFA
HHDF HHDFL HHDFA	19	HFS5	90	107	41	29	5.3	9	5	64	CBM5-10	2	HNTT5-5	2			
	20	HFS6	93.5	112	44	31	6.5	10.5	5	110	CBM6-12		HNTT6-6				
	26	HFS8 HFS8-45	130	149	57	40	8.5	13.3	5	250	CBM8-15		HNTT8-8				

Ordering Example

Part Number: HHDF19

Days to Ship **Configure Online**

Alterations **Part Number** - (SET / SST) **When SET is specified, product is not RoHS compliant.**
HHDF19 - SET

Alteration	Code	Spec.	No.	Price Adder
Applicable Screw and Nut Set	SET	Applicable screws and nuts come in a set.	19	
	SST	When SST is specified, screws and nuts will be in stainless steel.	20	
	(Stainless Steel)		26	

Price **Configure Online**

Pull Handles for Aluminum Extrusions / Pull Handles for Panels

Nylon Pull Handles **RoHS10**

UPCN (Nylon 6)

Material: Glass Fiber Reinforced Nylon 6

Part Number		Color of Handle	H	Applicable Extrusion (Series)	h	L	L1	R	C	Lr	Lc	Allowable Load (N)	Mass (g)	Unit Price										
Type	A													B (Black)				W (White), M (Orange), R (Red), G (Green)						
														1- 9 pc(s).	10-14	15-19	20~	1- 9 pc(s).	10-14	15-19	20~			
UPCN	19	B (Black) W (White) M (Orange) R (Red) G (Green)	36	HFS5	30	90	108.5	5.5	9.5	11	6	500	23											
			51		45									24										
	21		36	HFS6	30	93.5	112	6.5	10.5	13	7		25											
			51		45									28										
	26		41	HFS8 HFS8-45	34	117	139	8.5	13.3	15	9		38											
			57		50									48										
	27		45		37	132	156	16	54															
			63		55					62														
			52		42	152	177	6.5	10.5	13	7		66											
	28		50		42	179	204	8.5	13.3	17	9		68											
			71		63								86											

The default color of handle will be black unless specified. The default H dimension will be A19-H36, A21-H36, A26-H41, A27-H45 and A28-H50 unless specified.

Ordering Example **Part Number** - **Color of Handle** - **H**
UPCN19 - B - 51

Days to Ship **Configure Online**

Alterations **Part Number** - **Color of Handle** - **H** - (SET / SST)
UPCN21 - B - 51 - SET

Alteration	Code	Spec.	No.	Price Adder
Applicable Screw and Nut Set	SET	Applicable screws and nuts come in a set.	19	
	SST	When SST is specified, screws and nuts will be stainless steel.	21	
	(Stainless Steel)		26	

When SET is specified, the product is not RoHS compliant.

Nylon Pull Handles Mounting Plates for Nylon Pull Handles **RoHS10**

UPCNAT

Material: 304 Stainless Steel

Part Number	L	L1	A	B	N	Handle	Reference Mass (g)	Unit Price	Volume Discount Rate
Type								1-9 pc(s).	10~
UPCNAT	90	108.5	19	9.25	5.5	UPCN19	31		
	93.5	112	21		6.5	UPCN21	36		
	117	139	26	11		UPCN26	55		
	132	156	27	12	8.5	UPCN27	64		
	179	204	28	12.5		UPCN28	88		

Pull Handles for Panels

HHDS
HHDSW
HHDSA
HHDS

Type	Material	Surface Treatment
HHDS	Polycarbonate (Black)	-
HHDSW	Polycarbonate (White)	-
HHDSA	Aluminum Casting Alloy 383.0 Baked Finish, Silver Metallic	-
HHDS	304 Stainless Steel	Buffed Finish

Part Number Type	L	L ₁	H	h	A	Mass (g)			Unit Price			
						HHDS, HHDSW	HHDSA	HHDS	HHDS	HHDSW	HHDSA	HHDS
HHDS HHDSW HHDSA HHDS	90	110	32	24	13	17	43	90				
	104	127	37	27.7	16	25	65	150				
	122	149	43.3	32.5	19	42	102	220				

Ordering Example **Part Number**
HHDS90

Days to Ship **Configure Online**

Price **Configure Online**

