

# Slot Covers

Aluminum / Low Profile

Accessories for Aluminum Extrusions

Slot Covers - Aluminum / Low Profile

**RoHS 10**

Type	Material	Surface Treatment
HSCZ HSCM	6063-T5 Aluminum Alloy Aluminum Alloy (JIS)	Anodize

Slot Covers (Aluminum Low Profile)

For HFS5 series

**HSCZ5**

For HFS6 series

**HSCZ6**

For HFS8 series

**HSCZ8**

For HFS8 / 45 series

**HSCZ845**

Slot Covers (Aluminum)

For HFS5 series

**HSCM5**

For HFS6 series

**HSCM6**

For HFS8, HFS8-45 Series

**HSCM8**


## Configurable Length (Aluminum)

Part Number	Length 1 mm Increment	Extrusions (Series)
HSCZ	5	HFS5
	6	HFS6
	8	HFS8
	845	HFS8-45

**Part Number Example**

Part Number	Length
HSCZ5	100
HSCM5	100


## Application Example



## Configurable Length (Aluminum)

Part Number	Length 1 mm Increment	Extrusions (Series)
HSCM	5	HFS5
	6	HFS6
	8	HFS8 HFS8-45

## Application Example



# Non-Slip, Seal & Protection Covers

Accessories for Aluminum Extrusions

Non-Slip, Seal & Protection Covers

**RoHS 10**

Material: EPDM Synthetic Rubber Hardness: Shore A60  
Heat Resistant Temperature: -40~120°C

Non-Plastic Covers

For HFS5 Series

**HSCG5**  
**HSCGF5**

For HFS6 Series

**HSCG6**  
**HSCGF6**

For HFS8 Series

**HSCG8**  
**HSCGF8**

For HFS8-45 Series

**HSCG845**  
**HSCGF845**

Seal Covers

For HFS5 Series

**HSCK5**  
**HSCKF5**

For HFS6 Series

**HSCK6**  
**HSCKF6**

HFS8 / HFS8-45 Series

**HSCK8**  
**HSCKF8**

Protection Covers

For HFS5 Series

**HSCD5**  
**HSCDF5**

For HFS6 Series

**HSCD6**  
**HSCDF6**

HFS8 / HFS8-45 Series

**HSCD8**  
**HSCDF8**

For HFS6 (30mm Angle) Series

**HSCWF6**

For HFS8 (40mm Angle) Series

**HSCWF8**

## Standard Length

Type	Part No.	Color	Length m	Extrusions (Type)
HSCG	5	B Black	12	HFS5
	6			HFS6
	8			HFS8
	845			HFS8-45
HSCK	5	S Light Gray	12	HFS5
	6			HFS6
	8			HFS8 / HFS8-45
HSCD	5	S Light Gray	12	HFS5
	6			HFS6
	8			HFS8 / HFS8-45

**Part Number Example**

Part Number	Color	Length
HSCG6	B	12
HSCGF845	S	1520

## Application Example



## Configurable Length

Type	Part No.	Color	Length 1 mm Increment	Extrusions (Type)
HSCGF	5	B Black	50-3000	HFS5
	6			HFS6
	8			HFS8
	845			HFS8-45
HSCKF	5	S Light Gray	50-3000	HFS5
	6			HFS6
	8			HFS8 / HFS8-45
HSCDF	5	S Light Gray	50-3000	HFS5
	6			HFS6
	8			HFS8 / HFS8-45
HSCWF	6	S Light Gray	50-2000	HFS6
	8			HFS8