

Pull Handles with Caps / Nylon Pull Handles

Nylon Pull Handles with Caps RoHS **UPCDG** (Nylon 6)

* Easier mounting is possible by the combination use with the Nuts for Handles below.

Material	
Material	Glass Fiber Reinforced Nylon 6

Part Number Type	L	L1	Allowable Load (N)	Unit Price	
				Mass (g)	
UPCDG	90	133	500	30	
	94	136.5		33	
	117	160		36	
	132	175		39	

Pull Handles with Caps RoHS

Type	Handle		Cap	
	Material	Surface Treatment	Material	Color
HHDG	Aluminum Casting Alloy 3033	Baked Finish	ABS Resin	White
HHDGS	304 Stainless Steel	Buffed Finish	ABS Resin	White

* Easier mounting is possible by the combination use with the Nuts for Handles below.

Part Number Type	L	Mass (g)	Applicable Screw and Nut Set		Unit Price	
			Screw	Quantity	HHDG	HHDGS
HHDG HHDGS	100	62	Flathead Screw M5	2		

Ordering Example: **Part Number** **UPCDG90** **HHDG100** **Days to Ship** [Configure Online](#) **Price** [Configure Online](#)

Nuts for Pull Handles RoHS **HHPUW**

Part Number Type	P	B	A	M	Handle	Unit Price	Volume Discount Rate
HHPUW	90	10	100	6	UPCDG90		
	100	12	110	5	HHDG100		

Ordering Example: **Part Number** **HHPUW90** **Days to Ship** [Configure Online](#)

Nylon Pull Handles RoHS **UPFN**

Material	
Handle	Glass Fiber Reinforced Nylon 6
Threaded Section	Brass (Insert)

Part Number Type	A	L	Color of Handle	L1	H	h	M (Coarse)	Allowable Load (N)	Mass (g)	Unit Price		
										B (Black)	W (White), M (Orange), R (Red)	
UPFN	26	105	B (Black)	121	37	29	6	500	55			
		110	W (White)						60			
		117	M (Orange) R (Red)						62			

*The default color of handle will be black unless specified.

Ordering Example: **Part Number** **UPFN26** - **L** **105** - **Color of Handle** **B** **Price** [Configure Online](#)

Days to Ship [Configure Online](#)

Aluminum Tube Pull Handles

Aluminum Tube Pull Handles - Small Diameter RoHS

UWAPNC **UWAPFC** (L Configurable Type)

UHFAPC **UHFAPFC** (L Configurable Type)

Name of Parts		Material
Tube	6063 Aluminum Alloy	
Elbow	Polycarbonate	

Part Number Type	L	Applicable Screw and Nut Set	Unit Price	
			UWAPNC	UHFAPC
UWAPNC UHFAPC	100	Hex Socket Head Cap Screw M6		
	150			
	200			
	250			
	300			

Part Number Type	L 1mm Increment	Applicable Screw and Nut Set	Unit Price	
			UWAPFC	UHFAPFC
UWAPFC UHFAPFC	100~150	Hex Socket Head Cap Screw M6		
	151~200			
	201~250			
	251~300			

Ordering Example: **Part Number** **UWAPNC200** **UWAPFC-237** **Price** [Configure Online](#)

* For L Dimensions, add "-" (hyphen).

Days to Ship [Configure Online](#)

Aluminum Tube Pull Handles RoHS

UWAPN **UWAPF** (L Configurable Type)

UHFAPN **UHFAPF** (L Configurable Type)

Name of Parts		Material
Tube	6063 Aluminum Alloy	
Elbow	Glass Fiber Reinforced Nylon	

Part Number Type	L	Applicable Screw and Nut Set	Unit Price	
			UWAPN	UHFAP
UWAPN UHFAP	150	Flathead Screw M8		
	200			
	250			
	300			
	400			
	500			
	600			

Part Number Type	L 1mm Increment	Applicable Screw and Nut Set	Unit Price	
			UWAPF	UHFAPF
UWAPF UHFAPF	100~150	Flathead Screw M8		
	151~200			
	201~250			
	251~300			
	301~400			
	401~500			
	501~600			

Ordering Example: **Part Number** **UWAPN150** **UHFAPF-185** **Price** [Configure Online](#)

* For L Dimensions, add "-" (hyphen).

Days to Ship [Configure Online](#)