


Captured Washer Phillips Hexagon Head Screws

Captured Washer Phillips Hexagon Head Screw

BSET
SBSET Stainless Steel



Type	Material	Washers	Surface Treatment
BSET	Structural Alloy Steel Screw: JIS 0209 (6g)	Spring Washers JIS B1251 Flat Washers JIS B1256	Trivalent Chromate
SBSET	304 Stainless Steel or Equivalent * Strength Class A2-50 Equivalent Screw: JIS 0209 (6g)	Spring Washers JIS B1251 Flat Washers JIS B1256	Barrel, Passivated

(a) is the max length (reference) between head surface and the complete thread.

M x P	A	E	C	D	(a)
4 x 0.7	7	2.8	7.0	10	3.0
5 x 0.8	8	3.5	8.5	12	4.4
6 x 1.0	10	4.0	11.5	13	5.4
8 x 1.25	13	5.5	14.5	18	8.4

Type	M - L	Available Types			
		BSET		SBSET	
		1-99	100+	1-99	100+
BSET	4 - 8				
	10	•	•	•	•
	12				
	14				
	16	•	•	•	•
	20	•	•	•	•
	25				
	30	•	•		
	35	•	•		
	40	•	•		
SBSET	5 - 10				
	12	•	•	•	•
	14	•	•	•	•
	16	•	•	•	•
	20	•	•	•	•
	25	•	•	•	•
	30	•	•	•	•
	35	•	•		
	40	•	•		
	45	•	•		
	6 - 10	•	•	•	•
	12				
	14	•	•	•	•
	16				

Type	M - L	Available Types			
		BSET		SBSET	
		1-99	100+	1-99	100+
BSET	6 - 20	•	•	•	•
	25	•	•	•	•
	30	•	•	•	•
	35	•	•		
	40	•	•		
	45	•	•		
	50	•	•		
	55	•	•		
	60	•	•		
	65	•	•		
SBSET	8 - 12	•	•	•	•
	14	•	•	•	•
	16	•	•	•	•
	20	•	•	•	•
	25	•	•	•	•
	30	•	•	•	•
	35	•	•		
	40	•	•		
	45	•	•		
	50	•	•		
	55	•	•		
	60	•	•		
	65	•	•		
	70	•	•		
	75	•	•		


Part Number Example **BSET5-10**

Precision Machine Screws / Ornamental Screws & Washers

Precision Machine Screws (Pkg)



PACK-MIB
PACK-SMIB Stainless Steel



Type	Material	Surface Treatment
PACK-MIB	SWCH Carbon Steel16A	Trivalent Black
PACK-SMIB	302 HQ Stainless Steel or Equivalent	—

No. 0, Type 1 Pan Head Screw

Type	Part Number								M x P	D	E	r (Max.)	(e) (Max.)	Pcs/Pkg
	M	L												
PACK-MIB PACK-SMIB	1.2	2	3	4	5	*6	*8	—	1.2 x 0.25	1.8	0.5	0.05	0.4	50
	1.4	2	3	4	5	6	8	—	1.4 x 0.3	2				
	1.6	2	3	4	5	6	8	—	1.6 x 0.35	2.4				
	1.7	2	3	4	5	6	8	—	1.7 x 0.35	2.5	0.5	0.6		
	2.0	2	3	4	5	6	8	—	2.0 x 0.4	3			0.6	
	2.5	—	3	4	5	6	8	*10	2.5 x 0.45	3.5				

The sizes marked by * are available for PACK-SMIB only.
When placing an order, please specify number of packages.


Part Number Example **PACK - MIB1.6 - 5**

Ornamental Screws & Washer



VIS Brass
VISS Stainless Steel

VISZ Brass
VIZS Stainless Steel



M (Coarse)	P (Pitch)	D
3	0.5	6
4	0.7	8
5	0.8	10
6	1.0	12

Type	Material	Surface Treatment
VIS	C2700 Brass (JIS) W	Nickel Plating
VISS	302 HQ Stainless Steel	—
VISZ	C2700 Brass (JIS) W	Nickel Plating
VIZS	303 Stainless Steel	—

Ornamental Screws

Part Number		Part Number		Part Number	
Type	M - L	Type	M - L	Type	M - L
VIS Brass	3 - 10	VIS Brass	5 - 10	VISS Stainless Steel	3 - 10
	15		15		15
	20		20		20
	25		25		25
	30		30		30
	35		35		4 - 10
	40		40		15
	45		45		20
	50		50		25
	50		50		30
	4 - 10		6 - 10		5 - 10
	15		15		15
	20		20		20
	25		25		25
	30		30		30
	35		30		6 - 10
	40		15		15
45	20	20			
50	25	25			
					30

Washers for Ornamental Screw

Part Number		d	t	Quantity
Type	d			
VISZ Brass	3	10	2	2500
	4	12	2.5	1400
	5	14	3	800
	6	16	3.5	500
VIZS Stainless Steel	3	10	2	500
	4	12	2.5	400
	5	14	3	300
	6	16	3.5	200

Part Number Example **VIS5-30**
VIZ24