


Sheet Metal Brackets

HFS5 Series




Features: Can be used for reinforcement of connecting extrusions.

Sheet Metal Brackets




Type	Material	Surface Treatment
HPTSS	Low Carbon Steel	Bright Chromate Plating
HPTSSL		
HPTSD		
SHPTSS	304 Stainless Steel	—
SHPTSSL		
SHPTSD		


HPTSS5
SHPTSS5



HPTSSL5
SHPTSSL5



HPTSD5
SHPTSD5




Part Number	Mass (g)	T	Applicable Screw and Nut			
			Screw	Qty.	Nut	Qty.
HPTSS5	11	2.3	M5-8	2	M5	2
SHPTSS5		2				
HPTSSL5	2.3					
SHPTSSL5	2					
HPTSD5	2.3					
SHPTSD5	2					

Sheet Metal Brackets




Type	Material	Surface Treatment
HPTLN	Low Carbon Steel	Trivalent Chromate
HPTLS	Low Carbon Steel	Bright Chromate Plating
HPTLD		
SHPTLN	304 Stainless Steel	—
SHPTLS		


HPTLN5 (Trivalent Chromate)
SHPTLN5



HPTLS5
SHPTLS5




HPTLD5



Part Number	Mass (g)	T	Applicable Screw and Nut			
			Screw	Qty.	Nut	Qty.
HPTLN5	41	3.2	M5-8	3	M5	3
SHPTLN5		2				
HPTLS5	3.2					
SHPTLS5	2					
HPTLD5	81	2.3				

Sheet Metal Brackets

HFS5 Series




Sheet Metal Brackets




Type	Material	Surface Treatment
HPTCUL	Low Carbon Steel	Trivalent Chromate
HPTUL		
HPTWUL		
SHPTCUL	304 Stainless Steel	—
SHPTUL		
SHPTWUL		


HPTCUL5 (Trivalent Chromate)
SHPTCUL5



HPTUL5 (Trivalent Chromate)
SHPTUL5



HPTWUL5 (Trivalent Chromate)
SHPTWUL5



Part Number	Mass (g)	T	Applicable Screw and Nut			
			Screw	Qty.	Nut	Qty.
HPTCUL5	95	2.3	M5-8	4	M5	4
SHPTCUL5	95	2		4		4
HPTUL5	380	2.3		7		7
SHPTUL5		2		7		7
HPTWUL5	378	2.3		12		12
SHPTWUL5		2				

Part Number Example: **Part Number** **HPTCUL5**

Part Number Alterations: **Part Number** - (SET) **HPTSS5** - SET

⚠ Not RoHS compliant when -SET specified.

Alteration	Code	Spec.	Plates, Brackets
Applicable Screws and Nuts Set	SET	Applicable screws and nuts for mounting each plate on extrusions come in a set. Materials: Low Carbon Steel, 304 Stainless Steel Set: Screw: CBM, Nut: HNNT, Screw: SCB, Nut: HNNTSN	HPTSS5 SHPTSS5 HPTSSL5 SHPTSSL5 HPTSD5 SHPTSD5 HPTLN5 SHPTLN5 HPTLS5 SHPTLS5 HPTLD5 HPTCUL5 SHPTCUL5 HPTUL5 SHPTUL5 HPTWUL5 SHPTWUL5

Application Example

