

**NEW**

**HI DURA RUBBER GRINDING WHEEL**

**RUBBER GRINDING WHEEL**

**HIGH DURABILITY RUBBER GRINDSTONE FOR POLISHING / RUBBER GRINDSTONE FOR POLISHING**



**Features**

- Highly durable, it undergoes very little deformation or wear.
- A rubber grindstone for polishing that uses high-durability, low-friction rubber and powder abrasive.

**Application**

- Ideal for surface finishing with emphasis on polishing performance. (Ferrous and non-ferrous metals: polishing, scratch and surface removing, surface polishing without deforming the workpiece, etc.)

**Supported materials**

- Alloys of iron, aluminum, nickel, zinc, titanium, copper, etc.

**Limit operational rotational speed**

- 30000 rpm

Part Number		Grain size (#)	Size (Grindstone dia. x grindstone length x shaft dia.)	Unit Price (10 pcs per set) 1~5 sets
Type	No.			
M-9XX	480	80	φ 4×13×3	Quotation
	680		φ 6×17×3	
	880		φ 8×20×3	
	1080		φ 10×20×3	
	4120	120	φ 4×13×3	
	6120		φ 6×17×3	
	8120		φ 8×20×3	
	10120		φ 10×20×3	
	4220	220	φ 4×13×3	
	6220		φ 6×17×3	
	8220		φ 8×20×3	
	10220		φ 10×20×3	
	4320	320	φ 4×13×3	
	6320		φ 6×17×3	
	8320		φ 8×20×3	
	10320		φ 10×20×3	
	4500	500	φ 4×13×3	
	6500		φ 6×17×3	
	8500		φ 8×20×3	
	10500		φ 10×20×3	
41000	1000	φ 4×13×3		
61000		φ 6×17×3		
81000		φ 8×20×3		
101000		φ 10×20×3		



**Features**

- Soft rubber with powerful self-regeneration achieves a soft polishing touch.
- A fine grindstone that does not cause scratches.

**Application**

- It can be used for polishing of any soft iron or stainless steel materials.
- Suitable for grinding and polishing of soft aluminum, resin, etc.

**Supported materials**

- Ferrous metals, non-ferrous metals, resins, etc.

**Limit operational rotational speed**

- 30000 rpm

Part Number		Grain size (#)	Size (Grindstone dia. x grindstone length x shaft dia.)	Unit Price (10 pcs per set) 1~5 sets
Type	No.			
M-DX	4120	120	φ 4×13×3	Quotation
	6120		φ 6×17×3	
	8120		φ 8×20×3	
	10120		φ 10×20×3	
	4320	320	φ 4×13×3	
	6320		φ 6×17×3	
	8320		φ 8×20×3	
	10320		φ 10×20×3	
	4600	600	φ 4×13×3	
	6600		φ 6×17×3	
	8600		φ 8×20×3	
	10600		φ 10×20×3	



Order

Part Number

M-9XX-480

M-DX-4120



Days to Ship

Quotation



Price

Quotation

MOLD MAINTENANCE RELATED PRODUCTS