

LOCATING PILOT PINS

Inlay female thread type RoHS **SKSTH** (Configurable P and B dimensions)

SKS3
60 ~ 63HRC


D _{g6}	M	L	S	Catalog No.		Base unit price 1~9 pieces
				Type	D	
5	-0.004 -0.012	3	12	SKSTH	5	8.00 ~ 8.99
					6	9.00 ~ 10.00
					8	10.00 ~ 10.99
8	-0.005 -0.014	4	15	SKSTH	8	11.00 ~ 12.00
					10	12.00 ~ 12.99
					13	13.00 ~ 16.00
10	-0.005 -0.014	5	20	SKSTH	10	14.00 ~ 14.99
					15	15.00 ~ 20.00
					17	16.00 ~ 16.99
13	-0.006 -0.017	6	25	SKSTH	13	17.00 ~ 20.00
					16	18.00 ~ 20.00

(Configurable P and B dimensions)

Order **Catalog No.** - P - B
SKSTH 8 - P12.80 - B3.5

Days to Ship **Quotation**

Price **Quotation**



Press-fit type RoHS **SFSTH** (Configurable P and B dimensions)

SKS3
60 ~ 63HRC

For (S), $S \approx 1.6 \times P$.


D _{m6}	L	Catalog No.		Base unit price 1~9 pieces
		Type	D	
4	+0.012	SFSTH	4	4.00 ~ 8.00
			5	5.00 ~ 10.00
			6	6.00 ~ 12.00
8	+0.015	SFSTH	8	8.00 ~ 14.00
			10	10.00 ~ 16.00
			13	13.00 ~ 18.00
13	+0.018	SFSTH	13	13.00 ~ 18.00
			16	16.00 ~ 20.00

(Configurable P and B dimensions)

Order **Catalog No.** - P - B
SFSTH 6 - P7.98 - B4.5

Days to Ship **Quotation**

Price **Quotation**



LOCATING PILOT PINS

RoHS **PST**

SKS3
60 ~ 63HRC

B	S	Catalog No.		Base unit price 1~9 pieces
		Type	D	
1	4	PST	1	1.50 ~ 3.00
			2	2.50 ~ 4.00
			3	4.00 ~ 6.00
2	7	PST	4	5.00 ~ 7.00
			5	6.00 ~ 8.00
			6	7.00 ~ 9.00
3	9	PST	8	9.00 ~ 13.00
			10	11.00 ~ 15.00

Order **Catalog No.** - L - P
PSTM 5 - 15 - P7.20

Alterations **Catalog No.** - L - P (PC) - (BC-PK)
PSTM 5 - 15 - P7.20 - BC3.5

Alteration	Code	Spec.	1Code
	PC	Tip diameter change PC ≥ Pmin. -0.2 0.01mm increments	Quotation
	BC	B dimension change 1 ≤ BC ≤ Bmax. 0.1mm increments S dimension remains the same.	
	PKC	Tip diameter tolerance change P +0.01/0 → +0.005/0	


RoHS **PSTM**

SKS3
60 ~ 63HRC

B	S	M	Catalog No.		Base unit price 1~9 pieces
			Type	D	
2	7	3	PSTM	5	6.00 ~ 8.00
				6	7.00 ~ 9.00
				8	9.00 ~ 13.00
3	9	PSTM	10	11.00 ~ 15.00	

Days to Ship **Quotation**

Price **Quotation**



RoHS **RFPP**

SK105 (Old JIS SK3)
55HRC ~

This product was discontinued in 2017.

H	L	(R)	P	Catalog No.		Base unit price 1~4 pieces
				Type	D	
35	90	5	29.5	RFPP	32	Quotation
					45	
48	110	8	44.5	RFPP	32	Quotation
					45	

Order **Catalog No.** - RFPP
RFPP 32

Days to Ship **Quotation**

Price **Quotation**

LOCATING COMPONENTS FOR AUTOMOTIVE DIES