

MATERIAL GUIDE ROLLER SETS

—BEARING TYPE—

MATERIAL GUIDE ROLLER SETS

—OIL-FREE BUSHING TYPE—

Single guide **GDRTA** (Roller bearing type)
GDRTB (Ball bearing type)

M8×1.25 (DP16)

Double guides **GDRTAW** (Roller bearing type)
GDRTBW (Ball bearing type)

This product was discontinued in 2017.
Catalog No. : GDRTAW GDRTBW

① SCM415
② 55HRC~

③ SS400
④ Hexagon socket head set bolt (Cone point)
Single guide 1 piece

Guide roller unit **GDRTAT** (Roller bearing type)
GDRTBT (Ball bearing type)

④ Hexagon socket head set bolt (Cone point) 1 piece

① Roller
② SCM415
③ 55HRC~

④ CSR (Spool retainer)
⑤ Hexagon socket head cap bolt
⑥ Oil-free bushing (LF type)
⑦ Snap ring (C type)
⑧ Spacer

⑨ Spring washer
D30---CBW10 1 piece
D55---CBW16 1 piece

Set parts

T	H	ℓ	d	A	B	C	P	R	E	F	D ₁	Catalog No. Type	D	W	Base unit price 1~9 sets Single guide
48	40	5	10	95	30	10	73	5.5	20	1.5	14	(Roller bearing type) GDRTA	30	38	Quotation
54	75	8	25	145	55	20	115	6.5	35	5.5	32	GDRTAW	55	70	
86	75	8	25	145	55	20	115	6.5	35	5.5	32	(Ball bearing type) GDRTB	30	38	
54	75	8	20	145	55	20	115	6.5	35	5.5	32	GDRTBW	55	70	

Individual parts

T	H	ℓ	d	F	D ₁	L	t	d ₁	S	N	Catalog No. Type	D	W	Base unit price 1~9 pieces
48	40	5	10	1.5	14	67	5.5	8	2.5	7	(Roller bearing type) GDRTA	30	38	Quotation
54	75	8	25	5.5	32	92	9.5	22	5	17	GDRTAT	55	70	
86	75	8	25	5.5	32	124	9.5	22	5	17	(Ball bearing type) GDRTBT	30	38	
48	40	5	9	1.5	12	67	5.5	7	2.5	7	GDRTB	30	38	
54	75	8	20	5.5	32	92	9.5	17	5	17	GDRTBW	55	70	

EX Example Example of mounting hole machining when used as individual parts

Fasten from the side using the provided hexagon socket screw.

Order Catalog No. — W
GDRTA 55 — 38

Price **Quotation**

Days to Ship **Quotation**

Single guide **EGDR**

Double guides **EGDRW**

This product was discontinued in 2017.
Catalog No. : EGDRW

① Roller
② SCM415
③ 55HRC~

④ CSR (Spool retainer)
⑤ Hexagon socket head cap bolt
⑥ Oil-free bushing (LF type)
⑦ Snap ring (C type)
⑧ Spacer

⑨ Spring washer
D30---CBW10 1 piece
D55---CBW16 1 piece

Guide roller unit **EGDRT**

④ Hexagon socket head set bolt (Cone point) 1 piece

① Roller
② SCM415
③ 55HRC~

④ CSR (Spool retainer)
⑤ Hexagon socket head cap bolt
⑥ Oil-free bushing (LF type)
⑦ Snap ring (C type)
⑧ Spacer

⑨ Spring washer
D30---CBW10 1 piece
D55---CBW16 1 piece

Set parts

T	H	ℓ	d	d ₁	A	B	C	P	R	E	F	D ₁	Catalog No. Type	D	W	Base unit price 1~9 sets Single guide
48	40	5	16	18	95	30	10	73	5.5	20	19	24	EGDR	30	38	Quotation
54	75	8	25	28	145	55	20	115	6.5	35	30.5	36	EGDRW	55	70	
86	75	8	25	28	145	55	20	115	6.5	35	30.5	36				

Individual parts

T	H	L	ℓ	d	F	S	D ₁	d ₁	M	Catalog No. Type	D	W	Base unit price 1~9 pieces
48	40	51	5	16	19	15	24	18	10	EGDRT	30	38	Quotation
54	75	59.5	8	25	30.5	26	36	28	16	EGDRT	55	70	
86	75	91.5	8	25	30.5	24	36	28	16				

Order Catalog No. — W
EGDR 55 — 38

Days to Ship **Quotation**

Price **Quotation**

Single guide **GDRA**

Double guides **GDRAW**

This product was discontinued in 2017.
Catalog No. : GDRAW

① SKS93
② 55~60HRC

③ SS400

Order Catalog No. — W
GDRA 30 — 38

Days to Ship **Quotation**

Price **Quotation**

T	H	W	ℓ	d	A	B	C	P	R	E	Catalog No. Type	D	Base unit price 1~9 pieces
50	40	40	5	10	90	30	10	66	5.5	20	GDRA	30	Quotation
70	70	54	8	25	130	50	15	100	6.5	30	GDRA	55	

CONVEYANCE COMPONENTS FOR AUTOMOTIVES