


## Information on Components Used


### Connector / Hood

**NFCN (excluding P.2249) / FCID Pressure Welding**



| Connector        |                         |
|------------------|-------------------------|
| Manufacturer     | FUJITSU Component       |
| Model Number     | <b>FCN-367J0**-AU-F</b> |
| Rated Current    | 1 ADC or less           |
| Rated Voltage    | 250 VAC or less         |
| More Information | <b>OP.65</b>            |


**NFCN (P.2249) / BHFCN / BLFCN / GLFN / FCHSK Soldering**



| Connector        |                       |
|------------------|-----------------------|
| Manufacturer     | FUJITSU Component     |
| Model Number     | <b>FCN-361*0**-AU</b> |
| Rated Current    | 3 ADC or less         |
| Rated Voltage    | 250 VAC or less       |
| More Information | <b>OP.64</b>          |

| Hood             |                      |
|------------------|----------------------|
| Manufacturer     | FUJITSU Component    |
| Model Number     | <b>FCN-360C0**-*</b> |
| More Information | <b>OP.66</b>         |

**NA40FM**



| FCN Connector    |                     |
|------------------|---------------------|
| Manufacturer     | TE                  |
| Model Number     | <b>1473381-1-MH</b> |
| Rated Current    | 3A or less / 1 Pole |
| Rated Voltage    | 250 VAC or less     |
| More Information | <b>OP.65</b>        |

| FCN Hood NA40FM  |                  |
|------------------|------------------|
| Manufacturer     | Misumi           |
| Model Number     | <b>BKH-FCN40</b> |
| More Information | <b>OP.67</b>     |

| CN2 Side MIL Connector |                          |
|------------------------|--------------------------|
| Manufacturer           | Hirose Electric Co., Ltd |
| Model Number           | <b>HIF3BA-40D-2.54R</b>  |
| Rated Current          | 1A                       |
| Rated Voltage          | 200 VAC                  |
| More Information       | <b>OP.48</b>             |

| CN2 Side MIL Hood |                       |
|-------------------|-----------------------|
| Manufacturer      | Misumi                |
| Model Number      | <b>NAH-MIL40</b>      |
| Remarks           | <b>Not in Catalog</b> |

Connector Included Cable Selection Method

Square Connector Included Cable

Coaxial Connector Included Cable

Round Connector Included Cable


Nylon Connector Included Cable

Custom Service

Connector Included Cable Documents


### Crimp Terminal

**SB**




| Y Type Crimp Terminals |                                    |
|------------------------|------------------------------------|
| Manufacturer           | Daido Solderless Terminal Mfg. Co. |
| Model Number           | <b>F0.3-3</b> Equivalent           |
| Size                   | 3.2mm                              |
| Outer Width            | 5.2mm                              |
| More Information       | <b>OP.468</b>                      |

**Others**




| Y Type Crimp Terminals |                                    |
|------------------------|------------------------------------|
| Manufacturer           | Daido Solderless Terminal Mfg. Co. |
| Model Number           | <b>F1.25-3.5</b> Equivalent        |
| Size                   | 3.7mm                              |
| Outer Width            | 6.0mm                              |
| More Information       | <b>OP.468</b>                      |

**WA / WB**



| Y Type Crimp Terminals |                                    |
|------------------------|------------------------------------|
| Manufacturer           | Daido Solderless Terminal Mfg. Co. |
| Model Number           | <b>F0.08-3</b> Equivalent          |
| Size                   | 3.2mm                              |
| Outer Width            | 5.2mm                              |
| More Information       | <b>OP.468</b>                      |

**Round Type Crimp Terminals**




| Round Type Crimp Terminals |                                    |
|----------------------------|------------------------------------|
| Manufacturer               | Daido Solderless Terminal Mfg. Co. |
| Model Number               | <b>0.3-3</b> Equivalent            |
| Size                       | 3.2mm                              |
| Outer Width                | 5.2mm                              |
| More Information           | <b>OP.464</b>                      |

The Y type crimp terminals are for M3 screw terminal block. The crimp terminal used is changed according to the thickness of the cable used.


### Multi-Core Cable

**SB Cable**




|                                   |                             |
|-----------------------------------|-----------------------------|
| Manufacturer                      | Misumi                      |
| Model Number                      | <b>SS30WS</b>               |
| Standard Acquired                 | AWM20276                    |
| Rated Temperature                 | 0 ~ 80°C                    |
| Flame Retardance                  | VW-1SC                      |
| Bending Radius mm (Fixed Parts)   | Finished Outer Diameter x 8 |
| Bending Radius mm (Movable Parts) | —                           |
| More Information                  | <b>OP.1339</b>              |

**F Cable**




|                                   |                             |
|-----------------------------------|-----------------------------|
| Manufacturer                      | Misumi                      |
| Model Number                      | <b>NA2464</b>               |
| Standard Acquired                 | AWM2464                     |
| Rated Temperature                 | 0 ~ 80°C                    |
| Flame Retardance                  | —                           |
| Bending Radius mm (Fixed Parts)   | Finished Outer Diameter x 8 |
| Bending Radius mm (Movable Parts) | —                           |
| More Information                  | <b>OP.1293</b>              |

**WA Cable**



|                                   |                              |
|-----------------------------------|------------------------------|
| Manufacturer                      | Misumi                       |
| Model Number                      | <b>MAST-UL20276SB-28</b>     |
| Standard Acquired                 | ULAWM20276                   |
| Rated Temperature                 | 0 ~ 80°C                     |
| Flame Retardance                  | VW-1                         |
| Bending Radius mm (Fixed Parts)   | Finished Outer Diameter x 10 |
| Bending Radius mm (Movable Parts) | —                            |
| More Information                  | <b>OP.1333</b>               |

**WB Cable**



|                                   |                             |
|-----------------------------------|-----------------------------|
| Manufacturer                      | Misumi                      |
| Model Number                      | <b>MAST-UL2464SB-28</b>     |
| Standard Acquired                 | ULAWM20276                  |
| Rated Temperature                 | 0 ~ 80°C                    |
| Flame Retardance                  | VW-1                        |
| Bending Radius mm (Fixed Parts)   | Finished Outer Diameter x 6 |
| Bending Radius mm (Movable Parts) | —                           |
| More Information                  | <b>OP.1285</b>              |