



Motor Type


Motor Manufacturer A (Panasonic Motor)
- Motor Type

	Constant Speed Motor	Variable Speed Motor
Model		
Feature	Motor suitable for continuous one-way operation	Motor that the speed can be infinitely variable by combining with a Speed Controller
Voltage	Single-Phase 100V, 110V, 115V, 200V, 220V, 230V Three-phase 200V, 220V, 230V	Single-Phase 100V, 110V, 115V, 200V, 220V, 230V
Continuous Operation	○	○
Instantaneous Reverse Operation	×	×
Variable Speed	×	○
Load Holding	×	×


Output	6W, 25W, 40W, 60W, 90W
Rated Voltage	100V, 110V, 115V, 200V, 220V, 230V
Voltage Range	±10% (In relation to Rated Voltage)*
Power Supply Frequency	50Hz/60Hz
Speed Control Range	90~1400min ⁻¹ (50Hz) 90~1700min ⁻¹ (60Hz)
Speed Fluctuation Ratio	5% (Std. Value)
Speed Setting	With a Potentiometer (Analog setting)
Operating Temperature	-10°C~40°C
Storage Temperature	-20°C~60°C
Operating Humidity	85%RH or less (No condensation)

*±10% is the voltage fluctuation range, and is not a continuously operable range.


- Motor Connection Diagram



- Speed Controller Specifications
- US Type for T Voltage Option




- MGSD Type for TA Voltage Option




⚠ A connector cable (1m) is included.
* For Panasonic Motor details, see P.977~

Motor Manufacturer B (Oriental Motor)
- Motor Connection Diagram



- Speed Controller Specifications



Motor cables are 0.5m long