




For Pricing and Days to Ship, Please Configure Online.

Conveyor Stands



Conveyor Legs (Mounting Brackets) / Transfer Roller

Conveyor Stand I Type



Conveyor Stand I Type (1 set)
CSTSA (Adjuster Type) **CSTSC** (Caster Type)

1 D dimension chart

X	50~100	101~
D	200	280

*X is conveyor mounting width.

The unit will not stand on its own.

	1 Bracket	2 Aluminum Extrusion	3 Base Plate	4 Level Adjusting Bolt	5 Caster
M Material	304 Stainless Steel	Aluminum	Steel	Steel	Plastic
S Surface Treatment	2B	Clear Anodize	Trivalent Chromate	Trivalent Chromate	-


The stands are shipped unassembled. Assembly by customers required.

Part Number Type	Shape	X 1mm Increment	L 10mm Increment	Main Body Price 1-5 Units
CSTS	A (Adjuster) C (Caster)	50~200	200~490	
			500~690	
			700~990	
			1000~1200	

Ordering Example: **Part Number** - X - L
CSTSA - X100 - L800

Days to Ship [Configure Online](#)

Conveyor Stand H Type



Conveyor Stand H Type (1 set)
CSTWA (Adjuster Type) **CSTWC** (Caster Type)

The unit will not stand on its own.

	1 Bracket	2 Aluminum Extrusion	3 Foot Base	4 Level Adjusting Bolt	5 Caster
M Material	Steel	Aluminum	Steel	Steel	Plastic
S Surface Treatment	Trivalent Chromate	Clear Anodize	Trivalent Chromate	Trivalent Chromate	-

The stands are shipped unassembled. Assembly by customers required.

Part Number Type	Shape	Y 1mm Increment	L 10mm Increment	Main Body Price 1-5 Units
CSTW	A (Adjuster) C (Caster)	150~600	200~490	
			500~690	
			700~990	
			1000~1200	

Ordering Example: **Part Number** - Y - L
CSTWC - Y500 - L1000

Days to Ship [Configure Online](#)

Conveyor Support Stands



CGF **W=60~150** **W=151~350**

When W=151 ~ 350, the number in () applies to the Hex Socket Set Screws (3) and (4). **M** Material: 304 Stainless Steel

W=Frame Width (See main conveyor pages)

Part Number	W 1mm Increment	H 1mm Increment	Unit Price 1 ~ 10 pc (s).
CGF	60~350	120~160	

For orders larger than indicated quantity, please request a quotation.

Ordering Example: **Part Number** - W - H
CGF - 220 - 120

Days to Ship [Configure Online](#)

Conveyor L Type Mounting Brackets



LGBR

M Material: 304 Stainless Steel

Part Number Type	W	L	P	G	Unit Price 1 ~ 10 pc (s).
LGBR	60	140	40	10	
		200			
	100	140	60	20	
		200			

For orders larger than indicated quantity, please request a quotation.

Ordering Example: **Part Number** - L
LGBR60 - 200

Days to Ship [Configure Online](#)

Transfer Roller



CGNR1 **CGNR2**

Install with good parallelism.
 Bushings are press-fit Cannot be removed.
 When selecting Plastic Rollers limit the load per roller to 3kgf or less.

	1 Bracket		2 Roller		3 Oil-Free Bushing
	Material	Surface Treatment	Material	Surface Treatment	
M Material	6063 Aluminum Alloy	Clear Anodize	Polyacetal	304 Stainless Steel	Ethylene tetrafluoride resin layer with filler material Sintered bronze layered steel back metal layer (Low Carbon Steel: Tin Plated)
S Surface Treatment	Clear Anodize	-	-	-	-

Applicable Conveyor: SVKA, SVKB

Part Number Type	Number of Rollers	Roller Material	W 1mm Increment	Unit Price (1-10 pc.)		
				W30-100	W101-200	W201-300
CGNR	1	P (Polyacetal)	30~300			
	2					
	1	S (304 Stainless Steel)				
	2					

For orders larger than indicated quantity, please request a quotation.

Ordering Example: **Part Number** - Material Code - W
CGNR1 - P - 100

Days to Ship [Configure Online](#)

