



Trims

Trims are available in 1m increment. Please note that ordering 5 pieces of L=100 means 5 rolls of 100 meter type.



Color - Pattern Samples


TR_T (Black - Extra Fine) B-5
 (White - Extra Fine) W-5
 TRCS (Gray - Wave) G-6
 (Black - Wave) B-6



Material Properties


Item	TPE	Silicon Rubber
Specific Gravity	0.95	1.2
Heat Resistance	+135°C	+200°C
Low Temp. Resistance	-60°C	-60°C
Compression Set	15~25%	16%

⚠️ TPE does not produce dioxin when burned.



Bending Directions

① ② ③



Applicable Plate Thickness

④

Feature

Because of the internal metal strip, it does not require adhesives to install.

Type	Material	
	Main Body	Internal Metal Strip
TR_T	Thermoplastic Elastomer (TPE)	Aluminum
TRCS	Silicon Rubber	Low Carbon Steel

Part Number Type	T	Color - Pattern	L	A	B	W	t	Minimum Bending Radius mm			Applicable Plate Thickness (T Range)
								Bending Directions①	Bending Directions②	Bending Directions③	
TRAT	0.4	B-5	L1~L100 (1m Increment)	4.4	9.7	0.4	1.9	30	30	20	0.3~0.8
	0.8			4.8	9.5	0.8					0.7~1.2
	1.6			5.6	9.1	1.6					1.2~1.6
	2.4			6.4	8.9	2.4					2.0~2.4
TRBT	0.8	B-5 W-5	L1~L100 (1m Increment)	5.6	11.3	0.8	2.3	40	40	20	0.6~1.2
	1.6			6.4	11.1	1.6					1.2~2.0
	2.4			7.2	11.0	2.4					2.0~3.0
	3.2			8.0	10.6	3.2					2.6~3.2
TRCT	1.6	B-5 W-5	L1~L100 (1m Increment)	6.0	14.5	1.6	2.2	30	30	30	1.2~2.4
	3.2			7.6	14.0	3.2					2.4~4.0
	4.8			9.2	13.3	4.8					4.0~5.0
	6.4			10.8	12.7	6.4					5.5~6.4
TRDT	3.2	B-5 W-5	L1~L100 (1m Increment)	7.8	19.0	3.2	2.3	50	50	50	2.3~4.0
	6.4			11.0	17.5	6.4					6.0~7.0
	8.0			12.6	16.7	8.0					7.0~8.5
	9.5			14.1	15.9	9.5					9.0~9.5
TRCS	3.2	G-6 B-6	L1~L75 (1m Increment)	9.6	13.2	4.6	2.5	50	50		1.0~3.2

⚠️ Minimum bending radius value is experimental ones and not guaranteed. Use them as reference.

Ordering Example: Part Number - Color - Pattern - L
 TRCT3.2 - B-5 - L6

Days to Ship [Configure Online](#)

Price [Configure Online](#)


Part Number Type	T	Color - Pattern	L	Unit Price/m						
				1~4m	5~9m	10~14m	15~29m	30~74m	75~99m	100m
TRAT	0.4	B-5	L1~L100 (1m Increment)							
	0.8									
	1.6									
	2.4									
TRBT	0.8	B-5 W-5	L1~L100 (1m Increment)							
	1.6									
	2.4									
	3.2									
TRCT	1.6	B-5 W-5	L1~L100 (1m Increment)							
	3.2									
	4.8									
	6.4									
TRDT	3.2	B-5 W-5	L1~L100 (1m Increment)							
	6.4									
	8.0									
	9.5									
TRCS	3.2	G-6 B-6	L1~L75 (1m Increment)							

⚠️ Specify L dimension in 1m increment.

Corner Trims


Corner Trims are offered for saving machining process. Trim's lip covers cut edge and uneven surface due to size.

Corner Trims




RoHS10


TRIN (for Internal Corner)



TROUT (for External Corner)



Applicable Plate Thickness



Feature

Because of the internal metal strip, it does not require adhesives to install.

Type	Material	
	Main Body	Internal Metal Strip
TRIN	Thermoplastic Elastomer (TPE)	Aluminum
TROUT	Thermoplastic Elastomer (TPE)	Aluminum

⚠️ Forcing trim to spread wide may split the welded part.

Part Number Type	T	Corner Direction	Color	L	A1	A	B1	B	W	Applicable Plate Thickness (T Range)	Applicable Trim	Unit Price 1 or 2 pc(s).	Volume Discount Rate 3 or 4 pcs.	Volume Discount Rate 5 pcs. or More
1.6	80	8.4	6.4	12.3	12.1	1.6	1.2~2.0	TRAT 1.6* TRBT 1.6						
2.4	100	9.2	7.2	12.2	12	2.4	2.0~3.0	TRAT 2.4* TRBT 2.4						
3.2	100	9.6	7.6	15.2	15	3.2	2.4~4.0	TRBT 3.2* TRCT 3.2						
TROUT	0.8	External Corner	B (Black)	50	7.6	5.6	13.5	12.3	0.8	0.6~1.2	TRAT 0.8* TRBT 0.8			
	1.6			80	8.4	6.4	12.3	12.1	1.6	1.2~2.0	TRAT 1.6* TRBT 1.6			
	2.4			100	9.2	7.2	12.2	12	2.4	2.0~3.0	TRAT 2.4* TRBT 2.4			
	3.2			100	9.6	7.6	15.2	15	3.2	2.4~4.0	TRBT 3.2* TRCT 3.2			

* While B dimension on trim side become shorter, lip part of the corner trim will cover the gap.

Ordering Example: Part Number - Color
 TRIN 0.8 - B

Days to Ship [Configure Online](#)

Example

