




For Pricing and Days to Ship, Please Configure Online.

## Safety Protection Materials


### D Type Rubber Bumpers

■ Hole Type is added to D Type Rubber Bumpers. Suitable for use in places where adhesives cannot be used or tight mounting is necessary.




**RoHS10**

**Standard Type**



Adhesive

**Hole Type**



Material:  
Main Body: Ethylene Rubber (EPDM Synthetic Rubber)  
Adhesive Part: Acrylic Adhesives  
Hardness: Shore A60

**\* Hole Machining Details**

Type	Screw Nominal Dia.	d	d1
PRGDS (Black) PRGDSY (Yellow)	5	6.0	11.0
PRGDM (Black) PRGDMY (Yellow)	6	7.0	13.5

⚠Screw holes may be oval due to its machining characteristics.

Part Number	L (mm)	A	W	R1	R2	t	a	b	c	s	Weight (g)	Unit Price	
												PRGDS (Black) PRGDSY (Yellow)	PRGDM (Black) PRGDMY (Yellow)
Compact Type PRGDS (Black) PRGDSY (Yellow)	100	14	20	R10	R7	3	2	18	2	0.3	19		
	500										95		
	1000										190		
	1500										285		
	2000										380		
Standard Type PRGDM (Black) PRGDMG (Gray) PRGDMY (Yellow)	100	20	30	R15	R11	4	3	28	4	0.4	44		
	500										220		
	1000										440		
	1500										660		
	2000										880		

⚠Clean the mating surface off oil and dust. Peel off backing paper to adhere it to an object.  
⚠Can be cut with a utility knife. ⚠Adhesive Strength (180° Peeling): 16N/20mm Width (When affixed to 304 Stainless Steel) ⚠For properties, see the Ethylene Rubber on P371

#### Hole Machining Charge

Part Number	L (mm)	H (mm)	F (mm)	P (mm)	Hole Machining Charge															
					H															
PRGDS	500	1~5	F≥20	P≥100	1H	2H	3H	4H	5H	6H	7H	8H	9H	10H	11H	12H	13H	14H	15H	16H
PRGDSY	1000	1~10			-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PRGDM	1500	1~15			-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PRGDMY	2000	1~20			-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

⚠Can be cut with a utility knife. ⚠For properties, see the Ethylene Rubber on P371 ⚠Adhesive is not applied to Hole Type.



**Standard Type**  
Part Number - L  
PRGDSY - 100



Days to Ship [Configure Online](#)

#### Hole Type

Part Number - L - H - F - P  
PRGDMY - 1000 - 5H - F100 - P150




Price [Configure Online](#)

## Safety Protection Materials


### D Type Rubber Bumpers for Corner / Safety Tapes

■ Corner covers are added to D Type Rubber Bumpers.




**RoHS10**

**Standard Type**



Cross-section Shape

**Hole Type**



Material:  
Main Body: Ethylene Rubber (EPDM Synthetic Rubber)  
Adhesive Part: Acrylic Adhesives  
Hardness: Shore A60

**\* Hole Machining Details**

Type	Screw Nominal Dia.	d	d1
PRGDSCH (Black) PRGDSCHY (Yellow)	5	6.0	11.0
PRGDMCH (Black) PRGDMCHY (Yellow)	6	7.0	13.5

⚠Screw holes may be oval due to its machining characteristics.

■ Standard Type													
Part Number	L (mm)	A	W	R <sub>1</sub>	R <sub>2</sub>	t	a	b	c	s	Unit Price	Volume Discount Rate	
Type											1~3 pcs.	4~7 pcs.	8 pcs. or More
Compact Type PRGDSC (Black) PRGDSCY (Yellow)	70	14	20	R10	R7	3	2	18	2	0.3			
Standard Type PRGDMC (Black) PRGDMCY (Yellow)	100	20	30	R15	R11	4	3	28	4	0.4			

⚠Clean the mating surface off oil and dust. Peel off backing paper to adhere it to an object.  
⚠Can be cut with a utility knife. ⚠Adhesive Strength (180° Peeling): 16N/20mm Width (When affixed to 304 Stainless Steel) ⚠For properties, see the Ethylene Rubber on P371

#### Hole Type

Part Number	L (mm)	H (mm)	A	W	R <sub>1</sub>	R <sub>2</sub>	t	a	b	c	s	Unit Price	Volume Discount Rate	
Type												1~3 pcs.	4~7 pcs.	8 pcs. or More
Compact Type PRGDSCH (Black) PRGDSCHY (Yellow)	70	20	14	20	R10	R7	3	2	18	2	0.3			
Standard Type PRGDMCH (Black) PRGDMCHY (Yellow)	100	30	20	30	R15	R11	4	3	28	4	0.4			


⚠Can be cut with a utility knife. ⚠For properties, see the Ethylene Rubber on P371 ⚠Adhesive is not applied to Hole Type.




Part Number - L - H  
PRGDSCH - 70  
PRGDMCH - 100 - 30




[Configure Online](#)



#### Safety Tapes



**PRTRT**



Material: Main Body: Polyethylene Foam  
Surface: Polyethylene Print  
Adhesive Part: Acrylic Adhesives

Part Number		L (m)	Unit Price
Type	W Selection (mm)		
PRTRT	50	10	
	100		

⚠L dimension is in meters.



Price [Configure Online](#)



Part Number  
PRTRT50



[Configure Online](#)

Phone 1-800-681-7475  
(1-847-843-9105)

**MISUMI**  
<http://us.misumi-ec.com/>

Fax 1-800-681-7402  
(1-847-843-9107)