



For Pricing and Days to Ship, Please Configure Online.

Compact Trims For Plastic Cover

Compact Trims for Plastic Cover with adhesive type capable of easy installation.

For Plastic Cover

For Plastic Cover with Lip

For Plastic Cover
CTRRT

For Plastic Cover with Lip
CTRTRR

Material Properties

Item	TPE	Adhesive
Specific Gravity	0.95	-
Heat Resistance	+135°C	+88°C
Low Temp. Resistance	-60°C	-15°C
Compression Set	15~25%	-

Ⓜ TPE does not produce dioxin when burned.

Type	Material	
	Main Body	Adhesive
CTRRT CTRTRR	Thermoplastic Elastomer (TPE)	Sealant


Part Number	Type	T	Color	L (m)	Applicable Plate Thickness	Unit Price		
						1m	3m	5m
CTRRT		3.0	G (Gray)	L1 L3 L5	2.5~3.5			
		5.0			4.5~5.5			
CTRTRR		3.0	Y (Yellow)	L1 L3 L5	2.5~3.5			
		5.0			4.5~5.5			

Ordering Example: Part Number - Color - L
 CTRRT3.0 - G - L1
 CTRTRR5.0 - Y - L3


Price [Configure Online](#)

Days to Ship [Configure Online](#)


Example




Panel End Protection
CTRRT is attached on the panel edge to prevent interference and alert a collision.




Filling a Gap on One Door
CTRTRR is attached to the panel edge of one door. Suitable for applications such as filling a gap between an object and insulating from splash and sound.



Filling a Gap between Both Doors①
CTRTRR and CTRTRR are attached to the panel edge of both doors, filling a gap between panels.



Filling a Gap between Both Doors②
CTRTRR is attached to the panel edge of both doors, filling a gap between panels. (Either side can be opened first.)



Compact/Plastic Trims Square / U-Shaped

Compact trims with no internal metal strip are easy to cut and bend as needed. New "U-Shape" type that does not produce corners against the sheet metal when added.

Compact Trims - Square-U-Shape

CTRTE
CTRTS

CTRTR
CTRTRR

CTRTR
CTRTRR

CTRTR
CTRTRR

Material Properties

Item	EPDM Synthetic Rubber	Silicon Rubber
	Specific Gravity	1.2
Heat Resistance	120°C	170°C
Low Temp. Resistance	-40°C	-60°C
Compression Set	16%	27%

Ⓜ Adhesive tape P.469 ADTR (EPDM Synthetic Rubber) and ADTS (Silicon) are used.

Compact Trims are available in 1m increment. Please note that ordering 5 pieces of L=75 means 5 rolls of 75 meter type.

Part Number	Type	T	L 1m Increment	A	B	W	t	Minimum Bending Radius mm			Applicable Plate Thickness	Unit Price (1m)	
								Bending Directions ①	Bending Directions ②	Bending Directions ③		No Adhesive Tape	W/ Adhesive Tape
Ethylene Rubber (EPDM Synthetic Rubber) Rectangular	CTRTE CTRTR (W/ Adhesive Tape)	1.6	L1-L75 (1m Increment)	5.2	10	1.4	1.9	R70	R50	R30	1.0~1.6		
		2.3		6	10	2.2	1.9				2.0~2.3		
		3.2		6.9	10	3.1	1.9				3.0~3.2		
		3.2		6	10	2.2	1.9				3.0~3.2		
Silicon Rubber Rectangular	CTRTR CTRTRSS (W/ Adhesive Tape)	1.6	*W/ Adhesive Tape *L1-L2	5.2	10	1.4	1.9	R30	R30	R30	1.0~1.6		
		2.3		6	10	2.2	1.9				2.0~2.3		
		3.2		6.9	10	3.1	1.9				3.0~3.2		
		3.2		4	6	1	1.4				0.6~1.2		
Ethylene Rubber (EPDM Synthetic Rubber) U-Shape	CTRTR CTRTRSS (W/ Adhesive Tape)	1.6		4.4	7	1.4	1.4				1.0~1.6		
		2.3		5.3	8	2.1	1.5				2.0~2.3		

Ordering Example: Part Number - L
 CTRTE1.6 - L32

Days to Ship [Configure Online](#)

Price [Configure Online](#)

Translucent plastic trims blend well with painted sheet metal and stainless steel surfaces.

Plastic Trims

Type	Material
PTRTN	Nylon 6

Bending Directions

Part Number	Type	No.	L 1mm Increments	A	W	Minimum Bending Radius mm			Applicable Plate Thickness
						Bending Directions ①	Bending Directions ②	Bending Directions ③	
PTRTN		1	10~200	3.3	1.3	R150	R300	R200	1.0~1.1
		2		3.7	1.7				1.2~1.5
		3		4.4	2.4				1.6~2.2
		4		5.3	3.3				2.3~3.2

Ordering Example: Part Number - L
 PTRTN1 - 200

Days to Ship [Configure Online](#)

Price [Configure Online](#)

Part Number	Type	T	Unit Price										
			L 1mm Increments										
			10~200	201~400	401~600	601~800	801~1000	1001~1200	1201~1400	1401~1600	1601~1800	1801~2000	
PTRTN		1											
		2											
		3											
		4											