

# **Aluminum Extrusions (HFS6 Series)**

1 Slot (30, 60 mm Square)

**Aluminum Extrusions & Brackets** 







#### **Configurable Length Extrusions**

Part Number		L	Mass kg/m	Sectional Area	Cross Sectional Moment of Inertia mm <sup>4</sup>		
		0.5 mm Increment	Wass Kg/III	mm²	ℓx	ℓ <sub>y</sub>	
HFSF6		3030 50–4000	0.92	338	3.03 x 10 <sup>4</sup>	2.76 x 10 <sup>4</sup>	
HFSFB6 Black Anodize							
HFST6	2020		0.95	351	3.03 x 10 <sup>4</sup>	3.03 x 10 <sup>4</sup>	
HFSTB6 Black Anodize	3030						
HFSH6			0.93	345	2.69 x 10 <sup>4</sup>	3.23 x 10 <sup>4</sup>	
HFSC6			0.97	361	2.99 x 10 <sup>4</sup>	3.24 x 10 <sup>4</sup>	

### Fixed Length Extrusion (Effective Length 4,000 mm)

Fixed Length Extrusion (Effective Length 4,000 mm)								
Part Number		L	Sectional Area mm <sup>2</sup>	Cross Sectional Moment of Inertia mm <sup>4</sup>				
		mm		ℓx	lу			
KHFSF6			338	3.03 x 10 <sup>4</sup>	2.76 x 10⁴			
KHFSFB6 Black Anodize	3030		330	3.03 X 10	2.70 % 10			
KHFST6		4000	351	3.03 x 10 <sup>4</sup>	3.03 x 10 <sup>4</sup>			
KHFSTB6 Black Anodize		Effective Length	331	3.03 X 10	3.03 X 10			
KHFSH6			345	2.69 x 10 <sup>4</sup>	3.23 x 10 <sup>4</sup>			
KHFSC6			361	2.99 x 10 <sup>4</sup>	3.24 x 10 <sup>4</sup>			

① Part numbers beginning with the character "K" indicate Fixed Length Extrusion.







Part Number
Alterations
Alterations
Alterations
Alterations
Alterations are available for Configurable
Length Extrusions. For details, refer to
P.2862–2875

## **Aluminum Extrusions (HFS6 Series)**

2 Slots (30, 60 mm Square)



Features: Extrusions shaped with (1 x 2 slots). This shape is effective where loads apply.



### **Configurable Length Extrusions**

Part Number	L 0.5 mm Inc.	Mass kg/m	Sectional Area mm²	Cross Sectional Moment of Inertia mm <sup>4</sup>		
				lх	ℓу	
HFS6 Clear Anodize HFSB6 Black Anodize CAF6 Clear Coating	3060	50-4000	1.6	592	5.33 x 10 <sup>4</sup>	20.56 x 10 <sup>4</sup>
HFSL6 Clear Anodize HFSLB6 Black Anodize	3060	50-4000	1.29	476	4.87 x 10 <sup>4</sup>	17.87 x 10 <sup>4</sup>
GFS6 Clear Anodize	3060	50-4000	1.71	634	5.95 x 10 <sup>4</sup>	23.78 x 10 <sup>4</sup>

O Applicable to 6,000 mm depending on products.

① For some extrusions, MISUMI may be unable to accept the order.

### Fixed Length Extrusions (Effective Length 4,000 mm, 1,000 mm)

Part Number	L mm	Sectional Area mm²	Cross Sectional Moment of Inertia mm <sup>4</sup>		
			lх	ℓу	
KHFS6 Clear Anodize	3060	1000	592	5.33 x 10 <sup>4</sup>	20.56 x 10 <sup>4</sup>
KHFS6 Clear Anodize KHFSB6 Black Anodize KCAF6 Clear Coating KHFSY6 Baked-on Finish (Yellow)	3060	4000	592	5.33 x 10 <sup>4</sup>	20.56 x 10⁴
KHFSL6 Clear Anodize KHFSLB6 Black Anodize	3060	4000	476	4.87 x 10 <sup>4</sup>	17.87 x 10 <sup>4</sup>
KGFS6 Clear Anodize	3060	4000	634	5.95 x 10 <sup>4</sup>	23.78 x 10 <sup>4</sup>

① Part numbers beginning with the character "K" indicate Fixed Length Extrusion.

O "Effective Length 4,000 mm" represents the extrusion with 4,000 mm or more effective length. (several cm)





KHFS6-3060 - 4000



Alterations are available for Configurable Length Extrusions. For details, refer to **P.2862–2875**