
Retaining Rings

C-Type / E-Type (Box)




Retaining C-Ring

Туре	Material	Hardness
BOX-STWN	Spring Steel	44~53 HRC min.
BOX-STWS	304 Stainless Steel	36~44 HRC min.



- O Confirm detailed dimensions. R2459
 Can be ordered as single item. R2459
 Installation Tools are available. R2461
- Retaining Rings E-Type (Box)





Retaining Ring E Type

Туре	Material	Hardness	Surface Treatment
BOX-NETW	Spring Steel	44~53 HRC min.	Trivalent Chromate
BOX-NETWS	304 Stainless Steel	37~46 HRC min.	_



- Oconfirm detailed dimensions. P.2459
- ① Can be ordered as single item. P.2459 ① When you order, please specify the box quantity. Minimum order is 1 box.



BOX-STWN10 **BOX-NETWS3**

Part N	Part Number	
Туре	No.	Pcs./Box
	3	
	4	
	5	2,000
	6	
BOX-STWN	8	
DOX-21 WN	10	1.000
	12	1,000
	15	
	20	500
	25	


Part Number		Pcs./Box
Туре	No.	PCS./BOX
	4	
	5	2.000
	6	2,000
	8	
BOX-STWS Stainless Steel	10	1,000
	12	
	15	
	20	500
	25	

Part	Part Number Pcs./Box	
Туре	No.	PGS./DUX
	1.2	
	1.5	
	2	
	2.5	2.000
BOX-NETW	3	2,000
BUX-NETW	4	
	5	
	6	
	7	1,000
	8	1,000

Part Number		Pcs./Box
Туре	No.	FGS./DUX
	1.2	
	1.5	
	2	
	2.5	2,000
BOX-NETWS	3	
Stainless Steel	4	
	5	
	6	
	7	1,000
	8	1,000

Inserts

Thread / Tangless (Box)



M (Coarse)	Tap Pilot Hole Diameter (Reference)
3	3.11-3.20
4	4.16-4.29
5	5.18-5.33
6	6.22-6.40
8	8.28-8.48

- *M and L are sizes when inserted into tapped holes.
- $\ensuremath{\mathbf{0}}$ L dimension before insertion is shorter than that after insertion. O See special wrenches and how to use. P.2461
- ① Can be ordered as single item. P.2461



Туре	Material
BOX-TLTS	304 Stainless Steel
(After Insertion)	Groove
M	

M (Coarse)	Tap Pilot Hole Diameter (Reference)
2.5	2.60-2.65
3	3.12-3.20
4	4.17-4.30
5	5.16-5.33
6	6.25-6.42
8	8.31-8.52

- U L dimension before insertion is shorter than that after insertion.
- O See special wrenches and how to use. P.2461 ① Can be ordered as single item. P.2462
- ① When you order, please specify the box quantity. Minimum order is 1 box.



Part Number Example

BOX-HLTS5-10 BOX-TLTS2.5-3.8

Pa	rt Number	Pcs./Box
Туре	*M - L	PCS./BUX
	3 - 3	
	4.5	
	6	
	4 - 4	
	6	
	8	
	5 - 5	
BOX-HLTS Stainless Steel	7.5	100
	10	
	6 - 6	
	9	
	12	
	8 - 8	
	12	
	16	

Part Number		
Туре	*M - L	Pcs./Box
	2.5 - 2.5	
	3.8	
	5	
	3 - 3	
	4.5	
	6	
	4 - 4	
	6	
BOX-TLTS	8	100
Stainless Steel	5 - 5	
	7.5	
	10	
	6 - 6	
	9	
	12	
	8 - 8	
	12	
	16	

