


Captured Washer Phillips Pan Head Screws

Captured Washer Phillips Pan Head Screws

**NSET
SCBJ**



| M x P | A | E | C (Max.) | D | (a) | Cross Recess Number |
|------------|------|-----|----------|------|-----|---------------------|
| 2 x 0.4 | 3.5 | 1.3 | 4.0 | 6.0 | 2.1 | 1 |
| 2.5 x 0.45 | 4.5 | 1.7 | 4.8 | 6.5 | 2.7 | 1 |
| 2.6 x 0.45 | 4.5 | 1.7 | 4.8 | 7.5 | 2.7 | 1 |
| 3 x 0.5 | 5.5 | 2.0 | 5.5 | 8.0 | 3.0 | 2 |
| 4 x 0.7 | 7.0 | 2.6 | 7.0 | 10.0 | 4.4 | 2 |
| 5 x 0.8 | 9.0 | 3.3 | 8.5 | 12.0 | 5.4 | 2 |
| 6 x 1.0 | 10.5 | 3.9 | 11.5 | 13.0 | 6.9 | 3 |

| Type | Material | Washers | Surface Treatment |
|-------------|-----------------------------------|--|--------------------|
| NSET | SWCH Carbon Steel or Equivalent | Spring Washers JIS B 1251 Flat Washers JIS B 1256 | Trivalent Chromate |
| SCBJ | 304 Stainless Steel or Equivalent | Spring Washers JIS B 1251 Flat Washers JIS B 1256 | — |


| Part Number | Available Types | | | | | | | |
|----------------------|-----------------|-------|------|-----|------|-------|---------|------|
| | Type | M - L | NSET | | SCBJ | | | |
| | | | 1-99 | 100 | 1-29 | 30-99 | 100-149 | 150+ |
| NSET SCBJ | 2 - 4 | 5 | • | • | • | • | • | • |
| | | 6 | | | | | | |
| | | 8 | | | | | | |
| | | 10 | | | | | | |
| | 2.5 - 4 | 5 | — | — | | | | |
| | | 6 | — | — | • | • | • | • |
| | | 8 | — | — | | | | |
| | | 10 | — | — | | | | |
| | | 12 | — | — | | | | |
| | 2.6 - 4 | 5 | | | — | — | — | — |
| | | 6 | • | • | — | — | — | — |
| | | 8 | | | — | — | — | — |
| | | 10 | | | — | — | — | — |
| | | 12 | | | — | — | — | — |
| | 3 - 5 | 6 | • | • | — | — | — | — |
| 8 | | • | • | • | • | • | • | |
| 10 | | • | • | • | • | • | • | |
| 12 | | • | • | — | — | — | — | |
| 14 | | • | • | — | — | — | — | |
| 15 | | • | • | — | — | — | — | |
| 16 | | • | • | — | — | — | — | |
| 20 | | • | • | — | — | — | — | |
| 25 | | • | • | — | — | — | — | |
| 30 | | • | • | — | — | — | — | |
| 35 | | • | • | — | — | — | — | |
| NSET SCBJ | 4 - 5 | 6 | — | — | — | — | — | |
| | | 8 | • | • | • | • | • | |
| | | 10 | • | • | • | • | • | |
| | | 12 | • | • | — | — | — | — |
| | | 14 | • | • | — | — | — | — |
| | 5 - 8 | 10 | • | • | • | • | • | • |
| | | 12 | • | • | — | — | — | — |
| | | 14 | • | • | — | — | — | — |
| | | 16 | • | • | — | — | — | — |
| | | 20 | • | • | — | — | — | — |
| | | 25 | • | • | — | — | — | — |
| 6 - 10 | 12 | • | • | • | • | • | • | |
| | 14 | • | • | — | — | — | — | |
| | 16 | • | • | • | • | • | • | |
| | 20 | • | • | — | — | — | — | |
| | 25 | • | • | — | — | — | — | |
| | 30 | • | • | — | — | — | — | |
| | 35 | • | • | — | — | — | — | |
| | 40 | • | • | — | — | — | — | |
| | 45 | • | • | — | — | — | — | |
| | 50 | • | • | — | — | — | — | |

Part Number Example **SCBJ6-10**

Captured Washer Phillips Pan Head Screws

Captured Flat and Spring Washers Phillips Pan Head Screws

**PSET
PSETS**




| Type | Material | Washers | Surface Treatment |
|--------------|-----------------------------------|--|--------------------|
| PSET | SWCH Carbon Steel or Equivalent | Spring Washers JIS B 1251 Flat Washers JIS B 1256 | Trivalent Chromate |
| PSETS | 304 Stainless Steel or Equivalent | Spring Washers JIS B 1251 Flat Washers JIS B 1256 | — |

| M x P | A | E | C (Max.) | D | (a) | Cross Recess Number |
|---------|------|-----|----------|------|-----|---------------------|
| 3 x 0.5 | 5.5 | 2.0 | 5.5 | 6.0 | 3.0 | 2 |
| 4 x 0.7 | 7.0 | 2.6 | 7.0 | 8.0 | 4.4 | |
| 5 x 0.8 | 9.0 | 3.3 | 8.5 | 10.0 | 5.4 | |
| 6 x 1.0 | 10.5 | 3.9 | 11.5 | 11.5 | 6.9 | 3 |

Captured Spring Washer Phillips Pan Head Screws

**WSET
WSETS**



| Type | Material | Washers | Surface Treatment |
|--------------|-----------------------------------|--|--------------------|
| WSET | SWCH Carbon Steel or Equivalent | Spring Washers JIS B 1251 Flat Washers JIS B 1256 | Trivalent Chromate |
| WSETS | 304 Stainless Steel or Equivalent | Spring Washers JIS B 1251 Flat Washers JIS B 1256 | — |

| M x P | A | E | C (Max.) | (a) | Cross Recess Number |
|---------|------|-----|----------|-----|---------------------|
| 3 x 0.5 | 5.5 | 2.0 | 5.5 | 2.4 | 2 |
| 4 x 0.7 | 7.0 | 2.6 | 7.0 | 3.5 | |
| 5 x 0.8 | 9.0 | 3.3 | 8.5 | 4.3 | |
| 6 x 1.0 | 10.5 | 3.9 | 11.5 | 5.1 | 3 |

| Part Number | |
|-----------------------|--------|
| Type | M - L |
| PSET PSETS | 3 - 6 |
| | 8 |
| | 10 |
| | 12 |
| | 4 - 6 |
| | 8 |
| | 10 |
| | 12 |
| | 15 |
| | 5 - 8 |
| | 10 |
| | 12 |
| | 15 |
| | 6 - 10 |
| | 12 |
| 15 | |
| 20 | |

| Part Number | |
|-----------------------|--------|
| Type | M - L |
| WSET WSETS | 3 - 6 |
| | 8 |
| | 10 |
| | 12 |
| | 4 - 8 |
| | 10 |
| | 12 |
| | 15 |
| | 5 - 8 |
| | 10 |
| | 12 |
| | 15 |
| | 6 - 10 |
| | 12 |
| | 15 |
| 20 | |