

Dual Wheel Casters

continued



Casters / Adjustment Pads

Dual Wheel Casters

RoHS10

Shaft		Wheel
Material	Surface Treatment	Material (Color)
SWCH Carbon Steel	Trivalent Chromate	Nylon (Black)

Plate Type

CTGMP

CTGMPS

Screw-In

CTGMR

CTGMRS

Body Type	Part Number		H	B ₁	B ₂	(W)	d	r	E	Allowable Load (N)	Mass (g)
	Type	D									
Swivel Screw-In	CTGMP	40	55	41	10	16	5.1	43	15	200	60
		50	65	45	11	18					
Swivel Screw-In Brake	CTGMPS	40	55	41	10	16	5.1	47	15	200	65
		50	65	45	11	18					

Part Number Example

Part Number - M

CTGMP40 - 8

CTGMR40 - 8

Body Type	Part Number		M	H	B ₁	B ₂	(W)	Mounting Screw			r	E	Allowable Load (N)	Mass (g)
	Type	D						NB	NT	NL				
Swivel Screw-In	CTGMR	40	8	50	41	10	16	13	4	15	43	14.5	200	60
		50	12	63	45	11	18	19	6	14	51	18	300	100
Swivel Screw-In Brake	CTGMRS	40	8	50	41	10	16	13	4	15	47	14.5	200	65
		50	12	63	45	11	18	19	6	14	62	18	300	105

Dual Wheel Casters

RoHS10

CTEJN

CTEJNS

Shaft		Wheel
Material	Surface Treatment	Material (Color)
SWCH Carbon Steel	Trivalent Chromate	Elastomer (Black)

Body Type	Part Number		M	H	B ₁	B ₂	(W)	Mounting Screw			r	E	Allowable Load (N)
	Type	D						NB	NT	NL*			
Swivel Screw-In	CTEJN	40	8 10	43	44	12	20	14	5	12 (19)	39	15	392
		50	8 10 12	58	49	14	21	17	6	14	45.5	17	588
		60	8 12	69							50.5	17	980
		75A	12	85	64	19	27	21	8	22	63	20	1176
		75B	16							25			
Swivel Screw-In Brake	CTEJNS	40	8 10	43	44	12	20	14	5	12 (19)	42	15	392
		50	8 10 12	58	49	14	21	17	6	14	49	17	588
		60	8 12	69							55	17	980
		75A	12	85	64	19	27	21	8	22	70.5	20	1176
		75B	16							25			

Part Number Example

Part Number - M

CTEJNS50 - 10

* Dimensions in () are applied to M10.

Dual Wheel Casters

continued



Casters / Adjustment Pads

Dual Wheel Casters

RoHS10

CTYNB

CTYNBS

Shaft		Wheel
Material	Surface Treatment	Material (Color)
SWCH Carbon Steel	Trivalent Chromate	Nylon (Black)

Type	Part Number		M	H	B ₁	B ₂	(W)	Mounting Screws			r	E	Allowable Load (N)
	Type	D						NB	NT	NL			
Swivel Screw-In	CTYNB	40	10	44	44	12	20	14	5	19	39	15	392
		50	12	57.5	49	9.5	21	17	6	22	46	17	588
Swivel Screw-In + Brake	CTYNBS	40	10	44	44	12	20	14	5	19	42	15	392
		50	12	57.5	49	9.5	21	17	6	22	48	17	588

Part Number Example

Part Number - M

CTYNBS40 - 10

Dual Wheel Casters

RoHS10

CPNB

CPNBS

Insert Socket (Included)

Material: Nylon

Shaft		Wheel
Material	Surface Treatment	Material (Color)
SWCH Carbon Steel	Trivalent Chromate	Nylon (Black)

Body Type	Part Number		H	B ₁	B ₂	(W)	Mounting Section			r	E	Allowable Load (N)	Mass (g)
	Type	D					d	NT	NL				
Pin	CPNB	40	49	41	10	16	8	3	38	43	15	200	65
		50	60	45	11	18				51	18	300	95
Swivel Screw-In With Brake	CPNBS	40	49	41	10	16	8	3	38	47	15	200	70
		50	60	45	11	18				57	18	300	100

Part Number Example

Part Number

CPNB40