
# **Covers / Gasket for Sealable Lids / Stands for Open-Top Tanks**

**Outlet Shape Selectable Type** 


initary Pipes / Vacuum Piping Parts / Tanks




#### **Lids for Standard Open-Top Tanks**

| Part Number |                    | (D.)              | (D.)              | (D <sub>3</sub> ) | (T) |  |
|-------------|--------------------|-------------------|-------------------|-------------------|-----|--|
| Туре        | Tank Inner Dia (D) | (D <sub>1</sub> ) | (D <sub>2</sub> ) | (D <sub>3</sub> ) | (T) |  |
|             | 180                | 207               | 197               |                   |     |  |
|             | 210                | 236               | 226               |                   | 22  |  |
| TANCV       | 240                | 267               | 257               | 92                | 22  |  |
| IANGV       | 270                | 296               | 286               |                   |     |  |
|             | 300                | 330               | 320               |                   | 25  |  |
|             | 360                | 390               | 380               | 109               | 25  |  |

Part Number For Inlet Shape Selectable Type Part Number TANCV180





#### **Lids for Sealable Open-Top Tanks**

|                | -                  |             |                   |                   |                   |  |
|----------------|--------------------|-------------|-------------------|-------------------|-------------------|--|
| Pa             | rt Number          | Inlet Shape | (D <sub>1</sub> ) | (D <sub>2</sub> ) | (D <sub>3</sub> ) |  |
| Туре           | Tank Inner Dia (D) | TANCVS Only | (D <sub>1</sub> ) | (D <sub>2</sub> ) | (D <sub>3</sub> ) |  |
| Standard       | 180                |             | 206               | 198               | 175               |  |
| TANCVM         | 210                |             | 234               | 227               | 202               |  |
|                | 240                | ADEF        | 269               | 262               | 234               |  |
| Outlet Config. | 270                | ADEF        | 297               | 290               | 260               |  |
| Selectable     | 300                |             | 330               | 323               | 291               |  |
| TANCVS         | 360                | 1           | 390               | 382               | 352               |  |

When ordering Outlet Config. Selectable Sealable Open-Top Tanks, choose TANCVS, which is for liquid

| Part Number |                    | (D.) | (D.) |     |  |
|-------------|--------------------|------|------|-----|--|
| Туре        | Tank Inner Dia (D) | (D₁) | (D₂) | (T) |  |
|             | 180                | 195  | 177  | 13  |  |
|             | 210                | 226  | 205  | 16  |  |
| Seal        | 240                | 260  | 235  | 17  |  |
| TANSEL      | 270                | 288  | 266  | 17  |  |
|             | 300                | 321  | 296  | 17  |  |
|             | 360                | 380  | 358  | 16  |  |

① Features of Silicon Rubber P.2567. ① Features of Gasket for Sealing Cover P.3441.


| Part N          | Part Number           |     |                |                |                |                |  |
|-----------------|-----------------------|-----|----------------|----------------|----------------|----------------|--|
| Туре            | Tank Inner<br>Dia (D) | Н   | D <sub>1</sub> | D <sub>2</sub> | D <sub>3</sub> | H <sub>1</sub> |  |
| Stand<br>TANSTD | 180                   |     | 120            | 195            | 330            | 100            |  |
|                 | 210                   | 250 | 150            | 225            | 350            | 120            |  |
| TANSID          | 240                   |     | 180            | 255            | 370            | 140            |  |
|                 |                       |     |                |                |                |                |  |

① D<sub>1</sub> fits any of the outlet shapes of the Selectable Type.

**Application** 







### **Pressure Tanks**

#### **Overview**

#### **Features**


- (1) Pressure tanks are suitable for liquid pumping and vacuum defoaming.
- (2) There are three options for capacity and tank shape.
- (3) Number of holes on rid (0, 3–5) and hole size (Rc (PT) 1/8 3/8) are selectable.
- (4) Level gauge and float switch can be mounted as alteration.

#### **Product Overview**

- (1) Capacity: 1-22.5 ℓ
- (2) Material: 304 Stainless Steel
- (3) Finish: Buffing on inner and outer surface Polishing grade 400 (\*Note) Buff Polish Grade:
  - (a) 240 Coarse Buff Polish. High level of brightness or luster is not provided.
  - (b) 320 Standard Buff Polish
  - (c) 400 Fine Buff Polish Our product is provided with this type of polish.


#### **Condition of Use**

- (1) Operating Pressure Range: 0.5 Mpa or lower
- (2) Chemical Resistance: See Table 1 to the right for details.
- (3) 0-Ring: Physical Characteristics, Chemical Resistance P.3448. Oil Resistance - Solvent Resistance: See Table 2



## **Alteration: Pressure Tanks with Safety Function**

- (1) Safety Cover: Lifting the cover discharges the pressure, preventing inadvertent operation.
- (2) Support Angles: Prevent the tank from falling after detachment, improving safety.
- (3) Clamp Locating Tang: Use the tang to position the clamp in order to improve repeatability



### **Table 1: Stainless Steel Chemical Resistance Chart**


| Chemical Solution         | 304 Stainless Steel | Chemical Solution         | 304 Stainless Steel |
|---------------------------|---------------------|---------------------------|---------------------|
| Alcohol                   | Good                | Bicarbonate Soda          | Good                |
| Ether                     | Good                | Lactic Acid (5%, Boiled)  | Acceptable          |
| Ammonia Water             | Good                | Lactic Acid (10%, Boiled) | Poor                |
| Butyric Acid              | Good                | Sulfuric Acid (5%)        | Acceptable          |
| Salt (Dry)                | Good                | Sulfuric Acid (50%)       | Poor                |
| Vinegar                   | Good                | Chlorine Gas (Humid)      | Poor                |
| Dilute Nitric Acid        | Good                | Chlorine water            | Poor                |
| Concentrated Nitric Acid  | Poor                | Hydrochloric Acid         | Poor                |
| Acetic Anhydride          | Good                | Ferric Chloride           | Poor                |
| Acetic Anhydride (Boiled) | Poor                | Bromine                   | Poor                |

#### **Table 2: Stainless Steel Chemical Resistance Chart**

| Chemical Solution                      | Nitrile               | Fluorine   | <b>Chemical Solution</b> | Nitrile    | Fluorine   |
|--|-----------------------|------------|--------------------------|------------|------------|
| Gasoline, Light Oil                    | il Excellent Excellen |            | Trichloroethylene        | Acceptable | Excellent  |
| Benzene, Toluene                       | Acceptable            | Excellent  | Methyl Alcohol           | _          | Acceptable |
| Animal and Vegetable Oil               | Excellent             | Excellent  | Methylethylketone        | Poor       | Poor       |
| Diester Lubricating Oil                | Poor                  | Good       | Ethyl Acetate            | Poor       | Poor       |
| Phosphate-Chlorinated<br>Hydraulic Oil | Poor                  | Acceptable | Ether                    | _          | Poor       |

1 The information in Table 1 and Table 2 above is reference data and to be used only as a guide. Values may differ depending on operational conditions or operating environment

| Part No. | Name of Parts                             | Purpose   |
|----------|---|---|
| (1)      | Tank Body                                 | Container for liquid  |
| (2)      | Lid for Pressure Tank                     | Applies pressure and prevents contamination                 |
| (3)      | Tank Clamp                                | Fix body and lid  |
| (4)      | 0-Ring                                    | Seal for body and lid                                       |
| (5)      | Lower Limit Float Switch                  | Activates an alarm when the liquid level drops to low limit |
| (6)      | Relief Valve                              | Releases pressure   |
| (7)      | Regulator for Pressure Tank               | Controls pressure within tank                               |
| (0)      | Level Gauge ((8)-1 Stainless Steel Joint) | Dravidas visual visus of the liquid level                   |
| (8)      | Level Gauge ((8)-2 Teflon® Tube)          | Provides visual view of the liquid level                    |
| (9)      | Base                                      | Secures tank body   |







| Tune     | Provided Effective | (1) Safe   | ty Cover | (2) Supp   | ort Angle  |            | (3) Clamp Lo | cating Tang |    | 4.5               | (1-)              | (1-)              | <i>a</i> > | (1-)              | D.             |
|----------|--------------------|------------|----------|------------|------------|------------|--------------|-------------|----|-------------------|-------------------|-------------------|------------|-------------------|----------------|
| Туре     | Capacity Depth H   | <b>A</b> 1 | B1       | <b>A</b> 2 | <b>B</b> 2 | <b>A</b> 3 | <b>B</b> 3   | Н           | W  | (L <sub>1</sub> ) | (L <sub>2</sub> ) | (L <sub>3</sub> ) | (L4)       | (L <sub>5</sub> ) | P <sub>1</sub> |
|          | 1.6                | 40         | 55       |            |            | 30         | 10           | 10          | 8  | 68.5              | 133.9             | 57.8              | 30         | 84                | 25             |
| TNKA     | 2.2                | 40         | 55       | 35         | 15         | 35         | 13           | 10          | 10 | 00.5              | 155.9             | 37.0              | 30         | 90                | 30             |
| (P.3451) | 3.1                |            |          |            |            | 37         | 13           |             | 12 |                   | 140               |                   | 40         | 103               | 40             |
| (P.3431) | 4.4                | 55         | 70       | 50         | 20         | 31         | 10           | 14          | 12 | 77                | 145               | 67.8              | 40         | 131               | 60             |
|          | 11                 |            |          | 50         | 20         | 40         | 16           |             | 16 |                   | 150               |                   | 50         | 158               | 85             |
|          | 1                  | 40         | 55       | 35         | 15         | 30         | 10           | 10          | 8  | 68.5              | 133.9             | 578.8             | 30         | 84                | 25             |
| TNKB     | 2.9                |            |          | 33         | 15         | 37         | 13           |             | 10 |                   | 140               |                   | 40         | 103               | 40             |
| (P.3452) | 4.7                | 55         | 70       | 50         | 20         | 3/         | 16           | 14          | 12 | 77                | 145               | 67.8              | 40         | 131               | 60             |
|          | 10                 |            |          | 50         | 20         | 40         | 10           |             | 16 |                   | 150               |                   | 50         | 156               | 85             |
| TNKC     | 4–22.5             | _          | _        | _          | _          | 30         | 10           | 10          | 8  | _                 |                   |                   |            |                   |                |



#### Precautions for Use

- (1) Pressure tanks featured in this catalog are not classified as first-class or
- CAUTION (2) Please use in the operational conditions above. When applying pressure, use pressure gauge, relief valve and safety regulator for your safety.
  (3) When the internal pressure is high, never loosen clamps etc., that tighten lid and nozzle.
  - (4) Never use as a container to generate vapor by steaming, heating or as a result of



- (1) O-ring is used in the lid of this product. When closing the lid, please make sure the O-ring is securely fit into the groove on tank body.

  (2) Tighten the clamp by hand, then use a wrench to secure the clamp an extra half
- (3) Maximum operating pressure of the tank is 0.5 Mpa or less. Do not operate beyond the maximum pressure. Pressure relief valves are recommended when using tanks in
- (4) When loosening clamps, be sure to release the internal pressure by a relief valve etc, into the room condition. Also, confirm that the pressure gauge (regulator) indicates room pressure.



3448