

# LOCATION PINS

	<b>TLPA</b>  M S45C H 40 ~ 50HRC	<table border="1"> <thead> <tr> <th>D<sub>h7</sub></th> <th>L</th> <th>R</th> <th>d</th> <th>Catalog No.</th> <th>Base unit price</th> </tr> <tr> <th>Type</th> <th colspan="2">D</th> <th colspan="3">1~9 pieces</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>0 -0.021</td> <td>46</td> <td>3</td> <td>TLPA</td> <td>20</td> </tr> </tbody> </table>	D <sub>h7</sub>	L	R	d	Catalog No.	Base unit price	Type	D		1~9 pieces			20	0 -0.021	46	3	TLPA	20																											
D <sub>h7</sub>	L	R	d	Catalog No.	Base unit price																																										
Type	D		1~9 pieces																																												
20	0 -0.021	46	3	TLPA	20																																										
	<b>TLPB</b> This product was discontinued in 2017. Catalog No. : TLPA TLPB TLPC M S45C H 40 ~ 50HRC	<table border="1"> <thead> <tr> <th>D<sub>h7</sub></th> <th>L</th> <th>R</th> <th>d</th> <th>d<sub>1</sub></th> <th>H</th> <th>ℓ</th> <th>Catalog No.</th> <th>Base unit price</th> </tr> <tr> <th>Type</th> <th colspan="2">D</th> <th colspan="5">1~9 pieces</th> </tr> </thead> <tbody> <tr> <td>25</td> <td>0 -0.021</td> <td>30</td> <td>5</td> <td>10.5</td> <td>17.5</td> <td>12</td> <td>TLPB</td> <td>25</td> </tr> <tr> <td>32</td> <td>0 -0.025</td> <td>40</td> <td>5</td> <td>24</td> <td>10</td> <td>6</td> <td></td> <td>32</td> </tr> </tbody> </table>	D <sub>h7</sub>	L	R	d	d <sub>1</sub>	H	ℓ	Catalog No.	Base unit price	Type	D		1~9 pieces					25	0 -0.021	30	5	10.5	17.5	12	TLPB	25	32	0 -0.025	40	5	24	10	6		32										
D <sub>h7</sub>	L	R	d	d <sub>1</sub>	H	ℓ	Catalog No.	Base unit price																																							
Type	D		1~9 pieces																																												
25	0 -0.021	30	5	10.5	17.5	12	TLPB	25																																							
32	0 -0.025	40	5	24	10	6		32																																							
	<b>TLPC</b>  M S45C H 40 ~ 50HRC	<table border="1"> <thead> <tr> <th>D<sub>h7</sub></th> <th>D<sub>1h7</sub></th> <th>L</th> <th>R</th> <th>d</th> <th>b</th> <th>Catalog No.</th> <th>Base unit price</th> </tr> <tr> <th>Type</th> <th colspan="2">D</th> <th colspan="4">1~9 pieces</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>0 -0.021</td> <td>25</td> <td>0 -0.021</td> <td>44</td> <td>3</td> <td>10.5</td> <td>21</td> </tr> </tbody> </table>	D <sub>h7</sub>	D <sub>1h7</sub>	L	R	d	b	Catalog No.	Base unit price	Type	D		1~9 pieces				20	0 -0.021	25	0 -0.021	44	3	10.5	21																						
D <sub>h7</sub>	D <sub>1h7</sub>	L	R	d	b	Catalog No.	Base unit price																																								
Type	D		1~9 pieces																																												
20	0 -0.021	25	0 -0.021	44	3	10.5	21																																								
--Tapered type-- 	<b>LPU</b>  M S45C (Raw material)	<table border="1"> <thead> <tr> <th>D<sub>h7</sub></th> <th>ℓ</th> <th>d</th> <th>d<sub>1</sub></th> <th>H</th> <th>Catalog No.</th> <th>Base unit price</th> </tr> <tr> <th>Type</th> <th colspan="2">D</th> <th colspan="3">1~19 pieces</th> </tr> </thead> <tbody> <tr> <td>25</td> <td>0 -0.021</td> <td>12</td> <td>9</td> <td>14</td> <td>11</td> <td>LPU</td> <td>25</td> </tr> <tr> <td>32</td> <td>0 -0.025</td> <td>15</td> <td>11</td> <td>17.5</td> <td>13</td> <td></td> <td>30</td> </tr> <tr> <td>40</td> <td>0 -0.025</td> <td>18</td> <td>14</td> <td>20</td> <td>15</td> <td></td> <td>35</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>40</td> </tr> </tbody> </table>	D <sub>h7</sub>	ℓ	d	d <sub>1</sub>	H	Catalog No.	Base unit price	Type	D		1~19 pieces			25	0 -0.021	12	9	14	11	LPU	25	32	0 -0.025	15	11	17.5	13		30	40	0 -0.025	18	14	20	15		35								40
D <sub>h7</sub>	ℓ	d	d <sub>1</sub>	H	Catalog No.	Base unit price																																									
Type	D		1~19 pieces																																												
25	0 -0.021	12	9	14	11	LPU	25																																								
32	0 -0.025	15	11	17.5	13		30																																								
40	0 -0.025	18	14	20	15		35																																								
							40																																								
--Stepped type-- 	<b>LPL</b>  M S45C H 40 ~ 50HRC	<table border="1"> <thead> <tr> <th>D<sub>h7</sub></th> <th>D<sub>1h7</sub></th> <th>L</th> <th>B</th> <th>d</th> <th>d<sub>1</sub></th> <th>H</th> <th>Catalog No.</th> <th>Base unit price</th> </tr> <tr> <th>Type</th> <th colspan="2">D</th> <th colspan="5">1~19 pieces</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>0 -0.021</td> <td>25</td> <td>0 -0.021</td> <td>40</td> <td>20</td> <td>9</td> <td>11</td> <td>LPL</td> </tr> <tr> <td>25</td> <td>0 -0.021</td> <td>32</td> <td>0</td> <td>50</td> <td>25</td> <td>11</td> <td>17.5</td> <td></td> </tr> <tr> <td>32</td> <td>0 -0.025</td> <td>40</td> <td>0 -0.025</td> <td>70</td> <td>35</td> <td>11</td> <td>17.5</td> <td></td> </tr> </tbody> </table>	D <sub>h7</sub>	D <sub>1h7</sub>	L	B	d	d <sub>1</sub>	H	Catalog No.	Base unit price	Type	D		1~19 pieces					20	0 -0.021	25	0 -0.021	40	20	9	11	LPL	25	0 -0.021	32	0	50	25	11	17.5		32	0 -0.025	40	0 -0.025	70	35	11	17.5		
D <sub>h7</sub>	D <sub>1h7</sub>	L	B	d	d <sub>1</sub>	H	Catalog No.	Base unit price																																							
Type	D		1~19 pieces																																												
20	0 -0.021	25	0 -0.021	40	20	9	11	LPL																																							
25	0 -0.021	32	0	50	25	11	17.5																																								
32	0 -0.025	40	0 -0.025	70	35	11	17.5																																								
--Straight type-- 	<b>DLPA</b>  M S45C H 40 ~ 50HRC	<table border="1"> <thead> <tr> <th>D<sub>h7</sub></th> <th>L</th> <th>R</th> <th>d</th> <th>d<sub>1</sub></th> <th>H</th> <th>Catalog No.</th> <th>Base unit price</th> </tr> <tr> <th>Type</th> <th colspan="2">D</th> <th colspan="4">1~19 pieces</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>0 -0.021</td> <td>46</td> <td>3</td> <td>11</td> <td>—</td> <td>—</td> <td>DLPA</td> </tr> <tr> <td>25</td> <td>0 -0.021</td> <td>56</td> <td>3</td> <td>11</td> <td>12</td> <td>—</td> <td></td> </tr> <tr> <td>32</td> <td>0 -0.025</td> <td>70</td> <td>5</td> <td>11</td> <td>17.5</td> <td>24</td> <td></td> </tr> </tbody> </table> <p>⚡ D20 has a φ 11 through hole instead of a counterbore.</p>	D <sub>h7</sub>	L	R	d	d <sub>1</sub>	H	Catalog No.	Base unit price	Type	D		1~19 pieces				20	0 -0.021	46	3	11	—	—	DLPA	25	0 -0.021	56	3	11	12	—		32	0 -0.025	70	5	11	17.5	24							
D <sub>h7</sub>	L	R	d	d <sub>1</sub>	H	Catalog No.	Base unit price																																								
Type	D		1~19 pieces																																												
20	0 -0.021	46	3	11	—	—	DLPA																																								
25	0 -0.021	56	3	11	12	—																																									
32	0 -0.025	70	5	11	17.5	24																																									

Order Catalog No. **LPL 25**  
 Days to Ship **Quotation**  
 Price **Quotation**

Alterations Catalog No. — (LC)  
 LPU 25 — LC22  
**Quotation**

Alteration	Code	Spec.	1Code
	LC	Full length change 1mm increments $LPU = L - (\ell + 3) \leq LC < L$ $LPL = B + 2 \leq LC < L_{max}$ ⚡ Can be used for LPU and LPL only.	<b>Quotation</b>

# MAGNET LIFTER PINS

	<b>MLP</b>  Use at temperatures of 80°C or less.
--	--

Provided screw for fastening the magnet	Magnet	H	P	B Magnet length	d	Adhesive force N*	Surface magnetic flux density Gauss (G)	Catalog No.	L	Base unit price	
								Type	D	5mm increments	1~9 pieces
CB6	MG16	23	16	20	11	15.7	1200~1400	MLP	20	35~90	<b>Quotation</b>
CB8	MG20	28	20	25	14	29.4	1200~1500		25	40~100	
	MG28	35	28	30		78.5	1400~1700		32	45~100	

Order Catalog No. **MLP 20**  
 Days to Ship **Quotation**  
 Price **Quotation**

This product was discontinued in 2017.  
 Catalog No. : MLP

LOCATING COMPONENTS FOR AUTOMOTIVE DIES