



Please, refer to website for current Pricing and Lead Time

# High Pressure Steel Pipe Fittings

## -Different Pipe Threads-




# High Pressure Steel Pipe Fittings

## -Welded-

### Steel Pipe Fittings -Different Diameter Sockets-



Type	M
SGPSDJ	1025 Carbon Steel
SUTSSJ	304 Stainless Steel




Part Number	Rc (PT)	SGPSDJ	SUTSSJ	Unit Price	SGPSDJ	Unit Price	SUTSSJ				
Type	No.	T1	T2	L	(D)	L	(D)	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SGPSDJ	12	1/8	1/4	25	22	28	22				
	23	1/4	3/8	28	28	33	25				
	24	1/4	1/2	32	32	32	32				
	34	3/8	1/2	32	32	32	37				
SUTSSJ	36	3/8	3/4	38	38	38	42				
	46	1/2	3/4	38	38	38	42				
	48	1/2	1	45	46	45	45				
	68	3/4	1	45	46	45	45				

### Steel Pipe Fittings -Different Diameter Nipples-



Type	M
SGPNPJ	1025 Carbon Steel
STUPDJ	316 Stainless Steel




Part Number	R (PT)	SGPNPJ	STUPDJ	Unit Price	SGPNPJ	Unit Price	STUPDJ									
Type	No.	T1	T2	L	A	(B)	(l1)	(l2)	A	(B)	(l1)	(l2)	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SGPNPJ	12	1/4	1/8	32	8	17	14	10	-	-	-	-				
	23	3/8	1/4	36	9	21	14	13	9	19	14	13				
	24	1/2	1/4	39	9	26	17	13	9	23	17	13				
	34	1/2	3/8	40	9	26	17	14	9	23	17	14				
STUPDJ	36	3/4	3/8	43	10	32	19	14	-	-	-	-				
	46	3/4	1/2	46	10	32	19	17	10	29	19	17				
	48	1	1/2	49	11	35	21	17	12	35	20	17				
	68	1	3/4	51	11	35	21	19	11	35	21	19				

### Steel Pipe Fittings -Different Diameter Tees-



Type	M
SGPTDJ	1025 Carbon Steel
SUTPDJ	304 Stainless Steel




Part Number	Rc (PT)	SGPTDJ	SUTPDJ	Unit Price	SGPTDJ	Unit Price	SUTPDJ				
Type	No.	T1	T2	(A)	(B)	(A)	(B)	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SGPTDJ	34	1/4	1/2	28.5	33	28.5	33				
	34	3/8	1/2	28.9	33	28.9	33				
	36	3/8	3/4	35.1	38	35.1	38				
SUTPDJ	46	1/2	3/4	35.1	38	35.1	38				

### Steel Pipe Fittings -Bushings-



Type	M
SGPPBJ	1025 Carbon Steel
SUTPBJ	304 Stainless Steel



Part Number	T1	T2	SGPPBJ	SUTPBJ	Unit Price	SGPPBJ	Unit Price	SUTPBJ							
Type	No.	Rc (PT)	R (PT)	(B)	L	C	(l)	(B)	L	C	(l)	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SGPPBJ	12	1/8	1/4	17	20	5	15	14	17	5	12				
	23	1/4	3/8	19	22	7	15	19	18	5	13				
	24	1/4	1/2	23	26	9	17	23	21	5	16				
	26	1/4	3/4	29	29	9	20	29	24	6	18				
SUTPBJ	34	3/8	1/2	23	26	9	17	23	21	5	16				
	36	3/8	3/4	29	29	9	20	29	24	6	18				
	38	3/8	1	35	32	10	22	35	27	7	20				
	46	1/2	3/4	29	29	9	20	29	24	6	18				
SUTPBJ	48	1/2	1	35	32	10	22	35	27	7	20				
	68	3/4	1	35	32	10	22	35	30	7	20				

Material	Steel 1025 Carbon Steel of JIS G4051 or Equivalent Stainless Steel 304 Stainless Steel of JIS G3459 or Equivalent
Maximum Operating Temperature	1025 Carbon Steel 350°C 304 Stainless Steel 800°C
Max. Operating Pressure	20.6MPa (210kg/cm <sup>2</sup> )
Applicable Pipes	Piping with Carbon Steel Pipes, JIS G3454 · 3455 · 3456 Piping with Stainless Steel Pipes, JIS G3459


†1025 Carbon Steel material is made of JIS B2316 (2 column), while 304 Stainless Steel material is made of JIS B2316 (1 column).

Order Example **Part Number** **SGPSDJ12** **Days to Ship**

### High Pressure Welded Steel Pipe Fittings -Socket-




Type	M
SKPSH	1025 Carbon Steel
SKTSH	304 Stainless Steel




Part Number	Nominal	SKPSH					SKTSH					Unit Price	SKPSH	Unit Price	SKTSH
Type	No.	A	(B)	C	D	E	A	(B)	C	D	E	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SKPSH SKTSH	6A	1/8	11.0	19	12	7.1	6.4	11.0	19	10	7.1	6			
	8A	1/4	14.3	22	12	9.4	6.4	14.3	22	10	9.4	6			
	10A	3/8	17.8	28	13	12.7	6.4	17.8	25	10	12.7	6			
	15A	1/2	22.2	32	13	16.1	9.5	22.2	32	10	16.1	10			
	20A	3/4	27.7	38	16	21.4	9.5	27.7	38	13	21.4	10			
	25A	1	34.5	46	17	27.2	12.7	34.5	45	13	27.2	13			
	32A	1 1/4	43.2	58	18	35.5	12.7	43.2	55	13	35.5	13			
	40A	1 1/2	49.1	63	20	41.2	12.7	49.1	65	13	41.2	13			
	50A	2	61.1	76	23	52.7	19.1	61.1	75	16	52.7	19			

### High Pressure Welded Steel Pipe Fittings -Elbow-



Type	M
SKPLH	1025 Carbon Steel
SKTLH	304 Stainless Steel




Part Number	Nominal	SKPLH					SKTLH					Unit Price	SKPLH	Unit Price	SKTLH
Type	No.	A	(B)	C	D	E	A	(B)	C	D	E	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SKPLH SKTLH	6A	1/8	11.0	23	10.5	7.1	11.1	11.0	23	10.5	7.1	11.1			
	8A	1/4	14.3	23	10.5	9.4	11.1	14.3	23	10.5	9.4	11.1			
	10A	3/8	17.8	27	12	12.7	13.5	17.8	27	12	12.7	13.5			
	15A	1/2	22.2	34	13	16.1	15.9	22.2	34	13	16.1	15.9			
	20A	3/4	27.7	39	14	21.4	19.1	27.7	39	14	21.4	19.1			
	25A	1	34.5	47	16	27.2	22.2	34.5	47	16	27.2	22.2			
	32A	1 1/4	43.2	56	18	35.5	27.0	43.2	56	18	35.5	27.0			
	40A	1 1/2	49.1	63	19	41.2	31.8	49.1	63	19	41.2	31.8			
	50A	2	61.1	76	22	52.7	38.1	61.1	76	22	52.7	38.1			

### High Pressure Welded Steel Pipe Fittings -45° Elbow-



Type	M
SKPHEH	1025 Carbon Steel
SKTHEH	304 Stainless Steel




Part Number	Nominal	SKPHEH					SKTHEH					Unit Price	SKPHEH	Unit Price	SKTHEH
Type	No.	A	(B)	C	D	E	A	(B)	C	D	E	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SKPHEH SKTHEH	6A	1/8	11.0	23	10.5	7.1	7.9	11.0	23	10.5	7.1	7.9			
	8A	1/4	14.3	23	10.5	9.4	7.9	14.3	23	10.5	9.4	7.9			
	10A	3/8	17.8	27	11	12.7	7.9	17.8	27	11	12.7	7.9			
	15A	1/2	22.2	34	13	16.1	11.1	22.2	34	13	16.1	11.1			
	20A	3/4	27.7	39	14	21.4	12.7	27.7	39	14	21.4	12.7			
	25A	1	34.5	47	16	27.2	14.3	34.5	47	16	27.2	14.3			
	32A	1 1/4	43.2	56	18	35.5	17.5	43.2	56	18	35.5	17.5			
	40A	1 1/2	49.1	63	19	41.2	20.6	49.1	63	19	41.2	20.6			
	50A	2	61.1	76	21	52.7	25.4	61.1	76	21	52.7	25.4			

### High Pressure Welded Steel Pipe Fittings -Tees-



Type	M
SKPPTH	1025 Carbon Steel
SKTPTH	304 Stainless Steel



Part Number	Nominal	SKPPTH					SKTPTH					Unit Price	SKPPTH	Unit Price	SKTPTH
Type	No.	A	(B)	C	D	E	A	(B)	C	D	E	Qty. 1-9	10 or more	Qty. 1-9	10 or more
SKPPTH SKTPTH	6A	1/8	11.0	23	10.5	7.1	11.1	11.0	23	10.5	7.1	11.1			
	8A	1/4	14.3	23	10.5	9.4	11.1	14.3	23	10.5	9.4	11.1			
	10A	3/8	17.8	27	12	12.7	13.5	17.8	27	12	12.7	13.5			
	15A	1/2	22.2	34	13	16.1	15.9	22.2	34	13	16.1	15.9			
	20A	3/4	27.7	39	14	21.4	19.1	27.7	39	14	21.4	19.1			
	25A	1	34.5	47											