


Antislip Covers / Sealing Covers / Protection Covers / Panel Spacers / Magnetic Catch with Adhesive Tape



Antislip Covers

For HFS5 Series	For HFS6 Series	For HFS8 Series	For HFS8-45 Series
HSCG5 HSCGF5	HSCG6 HSCGF6	HSCG8 HSCGF8	HSCG845 HSCGF845

Sealing Covers

For HFS5 Series	For HFS6 Series	For HFS8, HFS8-45 Series
HSCD5 HSCDF5	HSCD6 HSCDF6	HSCD8 HSCDF8

Protection Covers

For HFS5 Series	For HFS6 Series	For HFS8, HFS8-45 Series	For HFS6 (30mm Angle) Series	For HFS8 (40mm Angle) Series
HSCW5 HSCWF5	HSCW6 HSCWF6	HSCW8 HSCWF8	HSCWF6	HSCWF8

Standard Length

Part Number	Type	No.	Color	Length m	Extrusion (Type)	Unit Price	Volume Discount Rate
HSCG	B (Black)	5	S (Light Gray)	12	HFS5		
		6			HFS6		
		8			HFS8		
HSCD	S (Light Gray)	5	S (Light Gray)	12	HFS5		
		6			HFS6		
		8			HFS8, HFS8-45		

Configurable Length

Part Number	Type	No.	Color	Length 1mm Increment	Extrusion (Type)	Unit Price/m
HSCGF	B (Black)	5	S (Light Gray)	50-3000	HFS5	
		6			HFS6	
		8			HFS8	
HSCKF	S (Light Gray)	5	S (Light Gray)	50-3000	HFS5	
		6			HFS6	
		8			HFS8, HFS8-45	
HSCDF	S (Light Gray)	5	S (Light Gray)	50-2000	HFS5	
		6			HFS6	
		8			HFS8, HFS8-45	
HSCWF	S (Light Gray)	5	S (Light Gray)	50-2000	HFS5	
		6			HFS6	
		8			HFS8	

Only light gray color is available for protection covers.

Only light gray color is available for protection covers.

Ordering Example: Part Number - Color - Length
HSCG6 - B - 12
HSCGF845 - S - 1520

Days to Ship: [Configure Online](#)

Price: [Configure Online](#)

ex Example

Protection of the corners of the aluminum extrusion with covers prevents the extrusion from damages by collisions occurring while moving.

Panel Spacers

HSCS5	HSCS6	HSCS8
HSCSF5	HSCSF6	HSCSF8

Color: Outgas Testing Results of S Panel Spacer

Measuring Method	GCMS	GCMS	GCMS	GCMS
Outgas	Acetaldehyde	1-Trimethylpentene	Dimethylnepthane	Xylene
60°C60min.	Below Detection Limit	Below Detection Limit	Below Detection Limit	Below Detection Limit
Detection Limit	0.01µg/g	0.01µg/g	0.01µg/g	0.01µg/g

Type	Color	Material	Heat Resistance Temperature
HSCS	Black	EPDM Synthetic	-40~120°C
	Light Gray	Rubber	
	Light Gray	Olefin Type Elastomer	

Standard Length

Part Number	Type	No.	Color	Length m	Extrusion (Series)	B (Black)	SE (Light Gray Economy)	S (Light Gray)
HSCS	B (Black)	5	SE (Light Gray Economy)	12	HFS5			
		6			HFS6			
		8			HFS8, HFS8-45			

Configurable Length

Part Number	Type	No.	Color	Length 1mm Increment	Extrusion (Series)	B (Black)	SE (Light Gray Economy)	S (Light Gray)
HSCSF	B (Black)	5	SE (Light Gray Economy)	100-3000	HFS5			
		6			HFS6			
		8			HFS8, HFS8-45			

Ordering Example: Part Number - Color - Length
HSCS5 - B - 12
HSCSF5 - SE - 1520

Days to Ship: [Configure Online](#)

Price: [Configure Online](#)

ex Example

- It can be used to fill a gap between the panel and the frame by using the mounting holes for a cover on a bracket.
- It can be also used as a stopper for panel doors.

Magnetic Catch with Adhesive Tape

Type	Material	Heat Resistance Temperature
HSMG	①Sponge ②Magnet	50°C

For HFS6 Series: **HSMG6**

For HFS8, HFS8-45 Series: **HSMG8**

① N Pole is marked. For mounting, refer to the Example.

Part Number	Type	No.	Color	Length mm	Extrusion (Type)	Magnet Type	Attraction Force per 100mm (g)	Surface Magnetic Flux Density Gauss (G)	Unit Price	Volume Discount Rate
HSMG	B (Black)	6	S (Light Gray)	1000	HFS6	Anisotropic Ferrite Magnet (Plastic Magnet)	75	500	1-4 pc(s)	5-20
		8							HFS8(-45)	

Attraction force is reference value at normal temperature (20°C). Can be used on door frames to be used as simplified magnetic catch.
 The attraction force is a reference value gained when two HSMG attracted each other.
 Can be cut with scissors.

Ordering Example: Part Number - Color
HSMG6 - B

Days to Ship: [Configure Online](#)

ex Example

- Peel off the backing paper to expose the adhesive.
- Attach it to the aluminum extrusion surface.