


Revolving Crank Handles with Square Bore - Retractable Handles / Revolving Crank Handles with Square, Round Bore / Revolving Crank Handles

Revolving Crank Handles with Square Bore - Retractable Handle

RoHS



Type	Body	Hub	Handle	Handle Thread	Included Screw
SSCH	Reinforced Nylon (Glass Fibers Contained)	1018 Carbon Steel Black Oxide	Phenol Resin	1018 Carbon Steel Trivalent Chromate	Structural Alloy Steel Trivalent Chromate




Part Number Type	W	L	A	H	h	D	K	F	M	B	d	b	Reference Mass (g)	Unit Price
		10	108	80	68	26	27.5	40	6	5	18	22	22	145
SSCH	12	130	100	72	30	31	40	10	5	18	27	27	210	
	14	164.5	130.5	102.5	35	36.2	65.3	9	6	23	30	30	310	
	17	198.5	161	122.5	40	40.5	80.3	12	8	26	34	34	420	

Revolving Crank Handles with Square/ Round Bore

RoHS



Type	Hub	Main Body, Handle	Screw	Handle Thread
Square Hole	Reinforced Nylon (Glass Fibers Contained)	1018 Carbon Steel Black Oxide	Brass (Insert)	1018 Carbon Steel Trivalent Chromate
Round Bore	Reinforced Nylon (Glass Fibers Contained)	1018 Carbon Steel Black Oxide	Brass (Insert)	1018 Carbon Steel Trivalent Chromate




Part Number	Type	L	A	H	h	D	K	F	M	B	d	b	h1	Reference Mass (g)	Unit Price
8	8	85.5	64.5	63	23	24.5	40	10	6	22	18	19	10	76	
10	10	105	80	76	26	27.5	50	13.5	6	22	22	22	11.5	102	
12	12	128	100	94.5	30	31	64.5	14.5	8	26	27	27	14.5	184	
14	-	161.5	130.5	114.5	35	36.2	79.5	19	8	26	30	30	-	259	
17	-	196	161	128.5	40	40.5	88.5	22	10	34	34	34	-	369	

Revolving Crank Handles

RoHS



Type	Offset Type	Material	Surface Treatment
NSCH	NOCH	Cast Iron Class No.30	Baked Paint Finish



Part Number	Type	L	A	H	h	D	d	d1	d2	K	F	M	B	Reference Mass (g)	Unit Price
8	8	86	63.5	75	22	27	22	18	14	49	13	32	5	105	
10	10	105	79	85	24	30	25	22	17	55	15	33	6	150	
12	12	128	98	105.7	28	34	28	26	20	70.7	17	38	8	230	
14	14	162	128	123.3	30	40	33	28	22	87.3	17	41	10	360	
17	17	198	159.5	128.3	34	45	37	32	25	87.3	21	50	10	510	
19	19	212	170	129.3	36	50	40	34	27	87.3	22	53	10	500	
22	22	212	170	129.3	36	50	40	34	27	87.3	22	53	10	680	

Ordering Example

Part Number
SSCH10
MBCH10
NSCH8

Days to Ship

Configure Online

Price

Configure Online

Spoked Handwheels

Spoked Handwheels

RoHS



I.D. Shaft Bore Shape	Type			Hub		Handwheel	Handle Mounting Hole Insert	Handle	Handle Thread	
	Stationary Handles	Fold-Down Revolving Handles	Without Handle	M Material	S Surface Treatment	M Material	M Material	M Material	M Material	S Surface Treatment
*1 Without Hole	PHLN	PHLFN	-	Cast Iron Class No.30	Black Oxide	Phenol	Brass	Phenol	1212 Carbon Steel	Trivalent Chromate
H9 Hole+Tap	-	-	PHLN-R			Nylon 6	12L13 Carbon Steel, Trivalent Chromate			
	PHLM	PHLFM	-	303 Stainless Steel	Black Oxide	Phenol	Brass			
H9 Hole+Keyway+Tap	PHLSM	-	-							
	PHLK	PHLFK	-	303 Stainless Steel	-	Polypropylene				
Square Hole	PHLSK	-	-	Cast Iron Class No.30	Black Oxide					
	PHLW	PHLFW	-	1045 Carbon Steel	Black Chromate					
Slit	PHLP	-	-							

