

Precision Ball Screws (Shaft Diameter 12, Lead 2, 4, 5, 10)

Accuracy Grade C3, C5, C7

Precision Ball Screws
(Shaft Diameter 12, Lead 2, 4, 5, 10) –
Accuracy Grade C3, C5, C7



RoHS10

Nut Type	Type	Accuracy Grade	Shaft Diameter	Lead	Screw Shaft		Nut	
					Material	Hardness	Material	Hardness
Standard Nut	BSX	C3	12	2	*4150 Alloy Steel	*Induction Hardened 58–62 HRC min.	JIS SCM420	Carburized 58–62 HRC min.
	BSS	C5		2, 4, 5, 10				
	BSSE	C7		2, 5, 10				
	BSSE	C7		2, 5, 10				

*For 1202, screw shaft material JIS-SCM415 Alloy Steel is carburized.

BSX1202

