


POSITIONING LOCKING BLOCKS

—WIDTH (A) • ANGLE (G) DESIGNATION TYPE (INLAY PART 4mm/8 • 10mm)—

Non JIS material definition is listed on P.1351 - 1352

Part Number	M	H
Inlay part 4mm		
LBCSF	SKS3	53~56HRC
LBCMF	HPM2T equivalent	37~41HRC

RoHS



■ Inlay part H=4mm

H	a	ℓ	ℓ_1	d_1	d_2	t	Part Number	Type	L	T	1mm increments	1° increments
4	6	6	13	9.5	5.5	6	LBCSF (SKS3)	10	20	10	13~ 48	5~33
	7	10	17	11	6.5	7		15		15	13~ 58	5~24
	8	13	21	14	9	9		20		20	18~ 98	5~18
	10	15	24	17	11.5	11		25		25	18~108	5~33
								10	30	15	*23~128	5~33
								15		20	(23~32: 1 bolt hole) (33~ : 2 bolt holes)	5~31
								25		25		5~26
								30		30		5~22
								35		25		5~28
										30		5~24
										35		5~21
										40		5~18

Please confirm and use the corresponding A • G selection type (LBCSK / LBCMK P.617) and A selection G designation type (LBCS / LBCM P.619).

Strength calculation for inlay sections P.1316

Order Part Number — T — A — G
LBCSF30 — 25 — A58 — G18

Days to Ship **Quotation**

Price **Quotation**

