

ANGLE AIR GRINDER / CUP GRINDSTONE

■ Application Use for deburring and chamfering molds.

■ Angle Air Grinder

M—AAG



■ Features

- The 120° angle makes it easy to work on corners. It is small, lightweight and high speed, improving work efficiency.

Body length	Screw dia.	Allowable rotational speed (rpm)	Supply air pressure (MPa)	Fitting	Hose length	Part Number	Unit Price 1~2 pcs
150	M7	22000	0.62	1/4	1300	M—AAG	Quotation



Order

Part Number

M—AAG



Days to Ship

Quotation



Price

Quotation

■ Cup Grindstone

M—CG



■ Application

- Cup grindstone for M—AAG.

Allowable rotational speed (rpm)	Grindstone dia. (φ)	Grain size (#)	Screw dia.	Part Number	Unit Price 1~5 pcs
23000	30	46	M7	M—CG—30—46	Quotation
		60		M—CG—30—60	



Order

Part Number

M—CG—30—60



Days to Ship

Quotation



Price

Quotation