











Copper Pipe Fittings (Brass Type)

Socket / Nipples / Female / Male Socket / Caps / Female / Male Elbow

Pipes / Fittings / Hoses / Valves

	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSFS</td><td>C36000 Brass</td></tr> </table>	Type	Material	SJSFS	C36000 Brass	
	Type	Material				
SJSFS	C36000 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSRN</td><td>C36000 Brass</td></tr> </table>	Type	Material	SJSRN	C36000 Brass	
	Type	Material				
SJSRN	C36000 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSXS</td><td>C36000 Brass</td></tr> </table>	Type	Material	SJSXS	C36000 Brass	
	Type	Material				
SJSXS	C36000 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSCP</td><td>C3604 Brass (JIS)</td></tr> </table>	Type	Material	SJSCP	C3604 Brass (JIS)	
	Type	Material				
SJSCP	C3604 Brass (JIS)					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSXL</td><td>C37700 Brass</td></tr> </table>	Type	Material	SJSXL	C37700 Brass	
	Type	Material				
SJSXL	C37700 Brass					
RoHS10						

Part Number		Rc (PT)	L	L ₁	B
Type	No.				
SJSFS	6A	1/8	21	10.5	14
	8A	1/4	28	14	17
	10A	3/8	32	16	21
	15A	1/2	40	20	26

Part Number		R (PT)	L	B
Type	No.			
SJSRN	6A	1/8	22	12
	8A	1/4	28	14
	10A	3/8	33	17
	15A	1/2	38	22

Part Number		Rc (PT)	R (PT)	L	d	B
Type	No.					
SJSXS	6A	1/8	1/8	20	5	14
	8A	1/4	1/4	24	8	17
	10A	3/8	3/8	28	11	21
	15A	1/2	1/2	33	15	26

Part Number		Rc (PT)	L	L ₁	B
Type	No.				
SJSCP	6A	1/8	9	7	12
	8A	1/4	11	9	16
	10A	3/8	14	12	19
	15A	1/2	15	13	24

Part Number		R, Rc (PT)	L ₁	L ₂
Type	No.			
SJSXL	6A	1/8	19	22
	8A	1/4	24	25
	10A	3/8	28	29
	15A	1/2	32	34

Fitting Specifications











Operating Temperature Range -50~280°C	-50~150°C (Not to be frozen)
Max. Operating Pressure	6.9 MPa

Part Number Example **SJSMT6A**

Copper Pipe Fittings (Brass Type)

Elbow / Male Elbow / Tees / Male Tees / Female Tees / Male Tees

Pipes / Fittings / Hoses / Valves

	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSFL</td><td>C37700 Brass</td></tr> </table>	Type	Material	SJSFL	C37700 Brass	
	Type	Material				
SJSFL	C37700 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSML</td><td>C37700 Brass</td></tr> </table>	Type	Material	SJSML	C37700 Brass	
	Type	Material				
SJSML	C37700 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSFT</td><td>C37700 Brass</td></tr> </table>	Type	Material	SJSFT	C37700 Brass	
	Type	Material				
SJSFT	C37700 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSMT</td><td>C37700 Brass</td></tr> </table>	Type	Material	SJSMT	C37700 Brass	
	Type	Material				
SJSMT	C37700 Brass					
RoHS10						
	<table border="1"> <tr><th>Type</th><th>Material</th></tr> <tr><td>SJSXT</td><td>C37700 Brass</td></tr> </table>	Type	Material	SJSXT	C37700 Brass	
	Type	Material				
SJSXT	C37700 Brass					
RoHS10						

Part Number		Rc (PT)	L ₁	L ₂
Type	No.			
SJSFL	6A	1/8	22	22
	8A	1/4	25	25
	10A	3/8	29	29
	15A	1/2	34	34

Part Number		R (PT)	L ₁	L ₂
Type	No.			
SJSML	6A	1/8	17	17
	8A	1/4	22	22
	10A	3/8	25	25
	15A	1/2	29	29

Part Number		Rc (PT)	L	L ₁
Type	No.			
SJSFT	6A	1/8	44	22
	8A	1/4	50	25
	10A	3/8	58	29
	15A	1/2	68	34

Part Number		R (PT)	L	L ₁
Type	No.			
SJSMT	6A	1/8	34	17
	8A	1/4	44	22
	10A	3/8	50	25
	15A	1/2	58	29

Part Number		R / Rc (PT)	L	L ₁	L ₂
Type	No.				
SJSXT	6A	1/8	44	22	19
	8A	1/4	50	25	24
	10A	3/8	58	29	28
	15A	1/2	68	34	32

Fitting Specifications

Operating Temperature Range -50~280°C	-50~150°C (Not to be frozen)
Max. Operating Pressure	6.9 MPa

Part Number Example **SJSMT6A**