SLOTTED KEYS

KFD KFS KEDS (Stainless steel) KESS (Stainless steel) KEGS (Stainless steel) Туре M KED KES KEG S450 JIS B1301-1996 Tensile strength: 600N/mm² or more KEDS KESS KEGS SUS316

Part Number			1		Н	С
Туре	E	3 _{h9}	<u> </u>	Tolerance		C
	2	0	0 15 20	2	0	
	3	-0.025	0 15 20 25 30	3	-0.025	0.16~0.25
	4		0 12 15 16 18 20 25 30 35 40 45 50	4		
KEDS (Stainless steel)	5	0 -0.030	0 12 15 16 18 20 25 30 35 40 45 50	5	$\begin{bmatrix} 0 \\ -0.030 \end{bmatrix}$	
NEDS (Stairless steel)	6		0 12 15 16 18 20 25 30 35 40 45 50 55 60	6]	0.25~0.40
1/20	7		15 20 25 30 35 40 45 50 55 60	7	-0.036	0.25~0.40
KES KESS (Stainless steel)	8	0 -0.036	15 16 18 20 25 30 35 40 45 50 55 60 70 80	7		
(Ottainios steel)	10		15 18 20 25 30 35 40 45 50 55 60 70 80	8		
1/20	12		20 25 30 35 40 45 50 55 60 70 80	7 °	0	
KEGS (Stainless steel)	14		30 35 40 45 50 55 60 70 80 90	9	-0.090	0.40 0.00
KEGS (Glainiess steel)	15	0 -0.043	30 35 40 45 50 55 60 70 80 90	10		0.40~0.60
	16	5.010	40 45 50 55 60 70 80 90 100	10		
	18		40 45 50 55 60 70 80 90 100 11	11	-0.110	

		.0				
Order	Pa	art N	umber	_	L	7
Order		KE	D6	_	30	





Tolerance

-Ŏ.15

-0.21

-0.25

Ŏ.30

12 15 16 18

35 40 45 50

55 60 70 80

90 100 110

20 25 30








Alteration	Code	Spec.	1Code	
Full length alteration	LC	Ldimension can be design increments. B LC range B 2 5 \cdot \chi \chi \chi \chi \chi \chi \chi \chi	ated in 1mm LC range $15 \sim 80$ $20 \sim 80$ $25 \sim 90$ $25 \sim 90$ $35 \sim 100$ $35 \sim 110$	Quotation

SHOT COUNTERS FOR MOLD


Non JIS material definition is listed on P.1351 - 1352



Inch screw

No.8-32UNC

M Glass-filled nylon housing



9|9|9|9|8|0

Serial number

1. Bore the holes for the counter and actuator rod to the dimensions shown in the figure below, from the rear of the movable mold plate. 2.Slot an opening for the display panel of the counter to the dimensions shown in the 3.Ensure that the actuator rod protrudes 4.0mm above the parting line and decide L dimension depending on the mold plate thickness. 4. Screw the actuator rod into the plunger and insert the counter from the rear of the mold plate. 5.Retain the bottom of the counter with the support plate.

nstallation dimension shown in above figure is just for reference purpose. Stroke distance of the counter pin for counting function is set at 3.75mm or more.

m:===

If the stroke is less than 3.75mm, the counter will not work. Conversely, when the stroke exceeds 4.25mm, the counter may be damaged.

art Number	U/Price 1~9	Part Number		
M-CVPL (only 1)	Quotation	M-CVEX (1)+(2)		

U/Price	Part	L	U/Price
1~9	Number	0.1mm increments	
Quotation	M-CVR	60.0~124.0	Quotation

4 ± 0.25 Support plate Movable mold plate (Movable mold plate side chart)

Plate thickness T

 $\pm 0.12 /$

M S45C

max.R0.75 Actuator Rod

A Actuator Rod

S Flectroless nickel plated

L=Movable mold plate thickness T+actuator rod protrusion of 4.0mm Specify taking into account the tolerance of the mold plate thickness T.

■Method of specifying the L dimension

The protruding part of the actuator rod is the stroke of the actuator rod. If the stroke is less than 3.75mm, the counter will not work. Conversely, if the stroke exceeds 4.25mm, the counter may be damaged when the mold closes.

■Features Notes

9999980 ////

- Counting is actuated mechanically, no miscount will occur if counter is installed correctly.
- Fach counter has a different serial number that will be used to identify the counter with the mold. Counters are sold in random order · ID Plate for tool identification is included for M-CVPL and M-CVEX only. Apply the adhesive seal at the back of the ID Plate to the front of the counter.
- The Counter is non-resettable mechanical. To represent the Formula testing purposes, the 7-digit indicator does not start from 0(a value of 9999980 will be shown). M — CVR Counter: Ensure that the actuator rod has a stroke of 4.0mm ± 0.25.













CounterView M Shot Counter is a registered trademark of Progressive Components International Corporation, covered by US Patent No.5,571,539, Canadian Patent No. 2,166,237, European Patent

CounterView™ Shot Counter is a registered trademark of Progressive Components International Corporation, covered by US Patent No. 5.271,539, Canadian Patent No. 2,166,237, European Patent No. EP726129, S.African Patent No. 2005/5337 and Asia and others pending.